

Sparepart documentation



BPT E 30 H

Prod. No.: 386608

Product details:

B.PROTHERM E 30 x 1/1 heated
B.PROTHERM E food transport container 1/1, convection-heated
Made of corrosion-resistant steel, with hinged door, mobile.
30 pairs of support ledges
Space between ledges: 38.3 mm
Temperature range adjustable between +30 °C and +95 °C.
Mains frequency: 50/60 Hz

Spareparts

Image	Code	Name	Quantity in device
	388087	Insert (valid from 12/16/2021)	1.0 Each
	386859	Adapter (valid from 12/16/2021)	4.0 Each
	386646	Spring VD-165 (valid from 07/28/2022)	1.0 Each
	246508	Pressure spring D-180-03 FA. GUTEKUNST (valid from 07/28/2022)	2.0 Each
	388101	Comfort opening right without drawbar (valid from 12/16/2021)	1.0 Each
	144218	PLUG-LAMINATE- 40X40X1,25 SERIES 120 (valid from 09/07/2022)	2.0 Each
	83031	washer A 8.4 DIN 125 brass (valid from 09/07/2022)	3.0 Each





Image	Code	Name	Quantity in device
	<u>388136</u>	Mounting bracket 80° (valid from 12/16/2021)	1.0 Each
	<u>386649</u>	Corpus hinge top right (valid from 12/16/2021)	1.0 Each
	<u>374840</u>	Rubber buffer D25xh12-d5 (valid from 12/16/2021)	1.0 Each
	<u>386867</u>	Tube Ø25x1,0 L=586,4 (valid from 12/16/2021)	1.0 Each
	<u>386569</u>	body for push handle holder Ø25 (valid from 12/16/2021)	2.0 Each
	<u>372913</u>	Cover push handle holder left, logo (valid from 12/16/2021)	1.0 Each
	<u>372912</u>	Cover push handle holder right, logo (valid from 12/16/2021)	1.0 Each
	<u>386652</u>	Hinge (valid from 12/16/2021)	1.0 Each
	<u>387165</u>	Warm module cpl. 950 W (valid from 01/05/2022)	1.0 Each



Image	Code	Name	Quantity in device
	<u>107469</u>	Radial Fan R2K150/0020-4218 (valid from 01/05/2022)	1.0 Each
	<u>388233</u>	Spring 6,9x8 VD_063H_20_1 (valid from 11/02/2022)	1.0 Each
	<u>107672</u>	Tubular heater 950W 20.43035.010 (valid from 01/05/2022)	1.0 Each
	<u>107694</u>	Temperature sensor PT1000_B. PROTHERM (valid from 01/05/2022)	1.0 Each
	<u>105805</u>	Safety temperature limiter 135 °C (valid from 01/05/2022)	1.0 Each
	<u>386579</u>	mold without lock (valid from 12/16/2021)	1.0 Each
	<u>386581</u>	mold with lock (valid from 12/16/2021)	1.0 Each
	<u>386673</u>	Lock (valid from 12/16/2021)	1.0 Each
	<u>70914</u>	Allen screw ISO 7380 M5x8 A2 m. Fl. (valid from 12/16/2021)	1.0 Each




Image	Code	Name	Quantity in device
	386903	Key <i>(valid from 12/16/2021)</i>	2.0 Each
	386766	Push Rod 30 <i>(valid from 12/16/2021)</i>	1.0 Each
	386771	Spring cpl. <i>(valid from 11/29/2022)</i>	1.0 Each
	388138	Knob cpl. <i>(valid from 12/16/2021)</i>	1.0 Each
	386565	Door handle <i>(valid from 12/16/2021)</i>	1.0 Each
	387941	Emergency opening <i>(valid from 12/02/2024)</i>	1.0 Each



Image	Code	Name	Quantity in device
	377734	Pressure spring VD-180-07 (valid from 08/03/2022)	2.0 Each
	386562	Cover (valid from 12/16/2021)	1.0 Each
	389058	Bushing (valid from 12/16/2021)	1.0 Each
	386778	Seal (valid from 12/16/2021)	3.188 Meter
	389005	Ventilation flap (valid from 08/09/2024)	1.0 Each
	365428	O-RING, 67.00 X 1.50 EPDM70 (valid from 12/16/2021)	1.0 Each
	386580	Retaining tube for ventilation flap (valid from 12/16/2021)	1.0 Each
	386547	Display Mount (valid from 01/05/2022)	1.0 Each
	107664	BPT Display (valid from 01/05/2022)	1.0 Each
	386476	Display Foil Atlas (valid from 01/05/2022)	1.0 Each
	369654	Plug holder universal (valid from 01/05/2022)	1.0 Each
	117766	plastic cover ring for plug holder (valid from 12/16/2021)	1.0 Each

Image	Code	Name	Quantity in device
	<u>105429</u>	terminal block Wieland KL 24/3 SL (valid from 01/05/2022)	1.0 Each
	<u>107722</u>	BPT Power PCB (valid from 01/05/2022)	1.0 Each
	<u>107666</u>	BPT Power PCB (max.) (valid from 01/05/2022)	1.0 Each
	<u>106304</u>	Cable gland M20x1.5 black (valid from 01/05/2022)	1.0 Each
	<u>106311</u>	Hexagon nut M20x1.5 (plastic) (valid from 01/05/2022)	1.0 Each
	<u>106708</u>	magnetic switch MK4-1A75-C-300W (valid from 01/05/2022)	1.0 Each
	<u>107692</u>	Decal equipotential bonding (valid from 01/05/2022)	1.0 Each
	<u>107682</u>	Spiral cable Europe 3x1,5 qmm BL-570 (valid from 05/23/2022)	1.0 Each
	<u>107683</u>	Spiral cable UK 3x1,5 qmm BL-570 (13A) (valid from 01/05/2022)	1.0 Each
	<u>107684</u>	Spiral cable CH 3x1,5 qmm BL-570 (10A) (valid from 01/05/2022)	1.0 Each



Image	Code	Name	Quantity in device
	<u>107687</u>	Spiral cable AUS 3x1,5 qmm B-570 10A (valid from 01/05/2022)	1.0 Each
	<u>107689</u>	Spiral cable Denmark 3x1,5 qmm B-570 13A (valid from 01/05/2022)	1.0 Each
	<u>107715</u>	Protective-socket Swiss-Standard T13 bla (valid from 01/05/2022)	1.0 Each
	<u>106803</u>	Build-in socket British standard (valid from 01/05/2022)	1.0 Each
	<u>106822</u>	Safety socket Denmark (valid from 01/05/2022)	1.0 Each
	<u>106737</u>	Build-in socket with pin (valid from 01/05/2022)	1.0 Each
	<u>107716</u>	Socket outlet protective contact-black (valid from 01/05/2022)	1.0 Each
	<u>106891</u>	seal for ABL electrical outlets (valid from 01/05/2022)	1.0 Each
	<u>386501</u>	Swivel castor 125 lock., DIN-PL (gray) (valid from 12/16/2021)	2.0 Each
	<u>382548</u>	Fixed wheel 125 DIN-PL, PA (gray) (valid from 12/16/2021)	2.0 Each







Image	Code	Name	Quantity in device
	362534	Cast. whl. 125 lock., DIN PL, CNS (valid from 12/16/2021)	2.0 Each
	368461	Fixed wheel 125 DIN-PL crs. CNS (valid from 12/16/2021)	2.0 Each
	386514	Swivel castor 125 lock, DIN-PL, PA, anti. (valid from 12/16/2021)	2.0 Each
	389841	Bearing plate (valid from 08/21/2024)	2.0 Each
	384208	Washer schnorr M6 type S A2 (valid from 08/21/2024)	2.0 Each
	70812	Bolt M6x60 ISO 7380 FL A2 (valid from 08/21/2024)	2.0 Each
	373392	Castor wheel with brake LE-VPP160R-FI-SG (valid from 12/16/2021)	2.0 Each
	373393	FIXED WHEEL B-VPP 160R-SG (valid from 12/16/2021)	2.0 Each
	373593	Swivel castor LE-POEV 160R-FI-SG 843898 (valid from 12/16/2021)	2.0 Each
	373594	Fixed castor B-POEV 160R-SG 843899 (valid from 12/16/2021)	2.0 Each

Image	Code	Name	Quantity in device
	<u>146794</u>	CASTER WHEEL LX-VPP 160XR-FI-SG (valid from 12/16/2021)	2.0 Each
	<u>146795</u>	FIXED WHEEL BX-VPP 160XR-SG (valid from 12/16/2021)	2.0 Each
	<u>373398</u>	Swivel castor LEX-POEV 160XR-SG-FI-84462 (valid from 12/16/2021)	2.0 Each
	<u>373399</u>	WHEEL, FIXED-BX-POEV 160XR-SG-844626 (valid from 12/16/2021)	2.0 Each
	<u>387228</u>	3-sided gallery for BPT E (valid from 12/16/2021)	1.0 Each
	<u>387226</u>	4-sided gallery for BPT E (valid from 12/16/2021)	1.0 Each
	<u>387196</u>	Bumper guard top cpl. (valid from 12/16/2021)	1.0 Each