

Sparepart documentation



BPT E 2 x 36 duo H/H banquet

Prod. No.: 386619

Product details:

B.PROTHERM E 2 x 36 x 2/1 duo heated/heated banquet
B. PROTHERM E food transport container 2/1, convection-heated
Made of corrosion-resistant steel, with hinged doors, mobile.
2 x 36 pairs of support ledges
Space between ledges: 38.3 mm
left compartment: convection-heated,
right compartment: convection-heated,
temperature range adjustable between +30 °C and +95°C.
Mains frequency: 50/60 Hz

Spareparts


Image	Code	Name	Quantity in device
	388087	Insert (valid from 02/15/2022)	2.0 Each
	388090	Pan cpl. (valid from 09/16/2022)	1.0 Each
	388101	Comfort opening right without drawbar (valid from 02/15/2022)	1.0 Each
	144218	PLUG-LAMINATE- 40X40X1,25 SERIES 120 (valid from 09/07/2022)	2.0 Each
	83031	washer A 8.4 DIN 125 brass (valid from 09/07/2022)	3.0 Each
	388103	Comfort opening left (valid from 02/15/2022)	1.0 Each
	386646	Spring VD-165 (valid from 07/28/2022)	1.0 Each
	246508	Pressure spring D-180-03 FA. GUTEKUNST (valid from 07/28/2022)	2.0 Each




Image	Code	Name	Quantity in device
	<u>388136</u>	Mounting bracket 80° (valid from 02/15/2022)	2.0 Each
	<u>386649</u>	Corpus hinge top right (valid from 02/15/2022)	1.0 Each
	<u>384619</u>	Grip (valid from 02/15/2022)	1.0 Each
	<u>374840</u>	Rubber buffer D25xh12-d5 (valid from 02/15/2022)	2.0 Each
	<u>386786</u>	Tube D28x1 L=586,4 (valid from 02/15/2022)	1.0 Each
	<u>372911</u>	body for push handle holder (valid from 02/15/2022)	2.0 Each
	<u>372913</u>	Cover push handle holder left, logo (valid from 02/15/2022)	1.0 Each
	<u>372912</u>	Cover push handle holder right, logo (valid from 02/15/2022)	1.0 Each
	<u>386652</u>	Hinge (valid from 02/15/2022)	2.0 Each



Image	Code	Name	Quantity in device
	<u>387165</u>	Warm module cpl. 950 W (valid from 02/15/2022)	2.0 Each
	<u>107469</u>	Radial Fan R2K150/0020-4218 (valid from 02/15/2022)	1.0 Each
	<u>388233</u>	Spring 6,9x8 VD_063H_20_1 (valid from 11/02/2022)	1.0 Each
	<u>107672</u>	Tubular heater 950W 20.43035.010 (valid from 02/15/2022)	1.0 Each
	<u>107694</u>	Temperature sensor PT1000_B. PROTHERM (valid from 02/15/2022)	1.0 Each
	<u>105805</u>	Safety temperature limiter 135 °C (valid from 02/15/2022)	1.0 Each
	<u>387304</u>	Warm module cpl. 1450W (valid from 04/18/2023)	2.0 Each
	<u>107671</u>	Tubular heater 1450W 20.43035.020 (valid from 02/15/2022)	1.0 Each
	<u>105194</u>	fixing clamp H3P-N66-NA (valid from 02/15/2022)	1.0 Each
	<u>387945</u>	Evaporator pan cpl. (valid from 09/16/2022)	1.0 Each



Image	Code	Name	Quantity in device
	<u>107667</u>	Vibratory pump 230-240V/50HZ (valid from 09/16/2022)	1.0 Each
	<u>107669</u>	Pump NME1 220V 60Hz (valid from 09/16/2022)	1.0 Each
	<u>387593</u>	Hose silicone ID 6 mm (valid from 09/16/2022)	0.25 Meter
	<u>387592</u>	Hose silicone ID 8mm (valid from 09/16/2022)	0.6 Meter
	<u>106303</u>	Screw joint, M16 black (valid from 09/16/2022)	1.0 Each
	<u>106310</u>	Hexagon nut, M16 (synthetic) (valid from 09/16/2022)	1.0 Each
	<u>107680</u>	Humidity sensor SP1 (HS13) (valid from 09/16/2022)	1.0 Each
	<u>386579</u>	mold without lock (valid from 02/15/2022)	1.0 Each
	<u>386581</u>	mold with lock (valid from 02/15/2022)	1.0 Each
	<u>386673</u>	Lock (valid from 02/15/2022)	1.0 Each
	<u>70914</u>	Allen screw ISO 7380 M5x8 A2 m. Fl. (valid from 02/15/2022)	1.0 Each




Image	Code	Name	Quantity in device
	386903	Key <i>(valid from 02/15/2022)</i>	2.0 Each
	386767	Push Rod 36 <i>(valid from 02/15/2022)</i>	1.0 Each
	386771	Spring cpl. <i>(valid from 11/29/2022)</i>	1.0 Each
	388138	Knob cpl. <i>(valid from 02/15/2022)</i>	1.0 Each
	386565	Door handle <i>(valid from 02/15/2022)</i>	1.0 Each



Image	Code	Name	Quantity in device
	387941	Emergency opening (valid from 12/02/2024)	1.0 Each
	377734	Pressure spring VD-180-07 (valid from 08/03/2022)	2.0 Each
	386562	Cover (valid from 02/15/2022)	1.0 Each
	389058	Bushing (valid from 02/15/2022)	1.0 Each
	386778	Seal (valid from 02/15/2022)	4.005 Meter
	387946	Emergency opening left (valid from 12/02/2024)	1.0 Each
	386547	Display Mount (valid from 02/21/2022)	2.0 Each
	107664	BPT Display (valid from 02/21/2022)	2.0 Each
	386476	Display Foil Atlas (valid from 02/21/2022)	2.0 Each
	369654	Plug holder universal (valid from 02/21/2022)	1.0 Each
	117766	plastic cover ring for plug holder (valid from 02/15/2022)	1.0 Each
	105429	terminal block Wieland KL 24/3 SL (valid from 02/21/2022)	2.0 Each
	107722	BPT Power PCB (valid from 02/21/2022)	2.0 Each

Image	Code	Name	Quantity in device
	<u>106304</u>	Cable gland M20x1.5 black (valid from 02/21/2022)	1.0 Each
	<u>106311</u>	Hexagon nut M20x1.5 (plastic) (valid from 02/21/2022)	1.0 Each
	<u>106708</u>	magnetic switch MK4-1A75-C-300W (valid from 02/21/2022)	2.0 Each
	<u>107692</u>	Decal equipotential bonding (valid from 02/21/2022)	1.0 Each
	<u>107682</u>	Spiral cable Europe 3x1,5 qmm BL-570 (valid from 05/23/2022)	1.0 Each
	<u>107683</u>	Spiral cable UK 3x1,5 qmm BL-570 (13A) (valid from 02/21/2022)	1.0 Each
	<u>107684</u>	Spiral cable CH 3x1,5 qmm BL-570 (10A) (valid from 02/21/2022)	1.0 Each
	<u>107687</u>	Spiral cable AUS 3x1,5 qmm B-570 10A (valid from 02/21/2022)	1.0 Each
	<u>107689</u>	Spiral cable Denmark 3x1,5 qmm B-570 13A (valid from 02/21/2022)	1.0 Each



Image	Code	Name	Quantity in device
	<u>373397</u>	Swivel castor LEX-POEV 160XR-SG-844624 (valid from 02/15/2022)	2.0 Each
	<u>373398</u>	Swivel castor LEX-POEV 160XR-SG-FI-84462 (valid from 02/15/2022)	2.0 Each
	<u>373399</u>	WHEEL, FIXED-BX-POEV 160XR-SG-844626 (valid from 02/15/2022)	2.0 Each
	<u>373393</u>	FIXED WHEEL B-VPP 160R-SG (valid from 02/15/2022)	2.0 Each
	<u>373394</u>	CASTER WHEEL LE-VPP 200R-SG (valid from 02/15/2022)	2.0 Each
	<u>373395</u>	CASTER WHEEL LE-VPP 200R-FI-SG (valid from 02/15/2022)	2.0 Each
	<u>373396</u>	FIXED WHEEL B-VPP 200R-SG- 763618 (valid from 02/15/2022)	2.0 Each
	<u>373400</u>	WHEEL, CASTER-LEX-POEV 200XR-SG-844628 (valid from 02/15/2022)	2.0 Each

Image	Code	Name	Quantity in device
	<u>373401</u>	WHEEL, CASTER LEX-POEV 200XR-SG-844629 (valid from 02/15/2022)	2.0 Each
	<u>373402</u>	Fixed castor BX-POEV 200XR-SG-844630 (valid from 02/15/2022)	2.0 Each
	<u>373391</u>	Castor wheel LE-VPP 160R-SG (valid from 02/15/2022)	2.0 Each
	<u>373392</u>	Castor wheel with brake LE-VPP160R-FI-SG (valid from 02/15/2022)	2.0 Each
	<u>373593</u>	Swivel castor LE-POEV 160R-FI-SG 843898 (valid from 09/14/2022)	2.0 Each
	<u>373594</u>	Fixed castor B-POEV 160R-SG 843899 (valid from 09/14/2022)	2.0 Each