

# Sparepart documentation

Kein Bild


## [TTW 30 EN PK](#)

**Prod. No.:** 390246


**Product details:**


Tray transport trolley, for passive cooling with eutectic plates,<br>3 compartments<br><br>Capacity: 30 Euronorm trays<br>insertion: lengthwise<br>Space between ledges: 115 mm<br>



### Spareparts



| Image                                                                               | Code                   | Name                                                            | Quantity in device |
|-------------------------------------------------------------------------------------|------------------------|-----------------------------------------------------------------|--------------------|
|   | <a href="#">144098</a> | Rubber buffer 12.5 rd form 2492<br>(valid from 03/05/2025)      | 37.0 Each          |
|  | <a href="#">350498</a> | Corpus hinge right cpl., passivated<br>(valid from 03/05/2025)  | 1.0 Each           |
|  | <a href="#">350496</a> | Corpus hinge left cpl., passivated<br>(valid from 03/05/2025)   | 1.0 Each           |
|  | <a href="#">373056</a> | Corner bumper bottom part<br>(valid from 03/05/2025)            | 1.0 Each           |
|  | <a href="#">372932</a> | Corner bumper both sides open<br>(valid from 03/05/2025)        | 1.0 Each           |
|  | <a href="#">372933</a> | Bumper corner open on one side left<br>(valid from 03/05/2025)  | 1.0 Each           |
|  | <a href="#">372934</a> | Bumper corner open on one side right<br>(valid from 03/05/2025) | 1.0 Each           |

| Image                                                                               | Code                   | Name                                                                  | Quantity in device |
|-------------------------------------------------------------------------------------|------------------------|-----------------------------------------------------------------------|--------------------|
|    | <a href="#">359327</a> | Insert for impact bar<br>(valid from 03/05/2025)                      | 4.0 Each           |
|    | <a href="#">284998</a> | Plastic locking<br>(valid from 03/05/2025)                            | 1.0 Each           |
|    | <a href="#">376576</a> | Door handle right - without lock<br>(valid from 03/05/2025)           | 1.0 Each           |
|                                                                                     | <a href="#">291538</a> | (valid from 03/05/2025)                                               | 1.0 Each           |
|    | <a href="#">284288</a> | Insert for door lock, not lockable<br>(valid from 03/05/2025)         | 1.0 Each           |
|                                                                                     | <a href="#">389922</a> | Lock - plastic, left<br>(valid from 03/05/2025)                       | 1.0 Each           |
|  | <a href="#">70914</a>  | Allen screw ISO 7380 M5x8 A2 m. Fl.<br>(valid from 03/05/2025)        | 4.0 Each           |
|  | <a href="#">81412</a>  | cylinder head screw ISO4762 M5x70<br>(valid from 03/05/2025)          | 4.0 Each           |
|  | <a href="#">284953</a> | Stopper<br>(valid from 03/05/2025)                                    | 1.0 Each           |
|                                                                                     | <a href="#">384218</a> | Corpus hinge right, bottom cpl., TTW H1<br>(valid from 03/05/2025)    | 1.0 Each           |
|                                                                                     | <a href="#">384219</a> | Corpus hinge left, bottom cpl., TTW H1<br>(valid from 03/05/2025)     | 1.0 Each           |
|                                                                                     | <a href="#">384213</a> | (valid from 03/05/2025)                                               | 1.0 Each           |
|                                                                                     | <a href="#">384212</a> | (valid from 03/05/2025)                                               | 1.0 Each           |
|  | <a href="#">284570</a> | SPRING,TENSION- 1.00x10.00x60.00<br>1.4310<br>(valid from 03/05/2025) | 1.0 Each           |
|                                                                                     | <a href="#">387796</a> | Plug SFL14<br>(valid from 03/05/2025)                                 | 4.0 Each           |

| Image                                                                               | Code                          | Name                                                                | Quantity in device |
|-------------------------------------------------------------------------------------|-------------------------------|---------------------------------------------------------------------|--------------------|
|    | <a href="#"><u>373392</u></a> | Castor wheel with brake LE-VPP160R-FI-SG<br>(valid from 03/05/2025) | 2.0 Each           |
|    | <a href="#"><u>373391</u></a> | Castor wheel LE-VPP 160R-SG<br>(valid from 03/05/2025)              | 2.0 Each           |
|    | <a href="#"><u>373395</u></a> | CASTER WHEEL LE-VPP 200R-FI-SG<br>(valid from 03/05/2025)           | 2.0 Each           |
|    | <a href="#"><u>373394</u></a> | CASTER WHEEL LE-VPP 200R-SG<br>(valid from 03/05/2025)              | 2.0 Each           |
|   | <a href="#"><u>373398</u></a> | Swivel castor LEX-POEV 160XR-SG-FI-84462<br>(valid from 03/05/2025) | 2.0 Each           |
|  | <a href="#"><u>373397</u></a> | Swivel castor LEX-POEV 160XR-SG-844624<br>(valid from 03/05/2025)   | 2.0 Each           |
|  | <a href="#"><u>373401</u></a> | WHEEL, CASTER LEX-POEV 200XR-SG-844628<br>(valid from 03/05/2025)   | 2.0 Each           |
|  | <a href="#"><u>373400</u></a> | WHEEL, CASTER-LEX-POEV 200XR-SG-844628<br>(valid from 03/05/2025)   | 2.0 Each           |
|                                                                                     | <a href="#"><u>291431</u></a> | Swivel castorLEX-POEV 200XR-IS-SG-867787<br>(valid from 03/05/2025) | 2.0 Each           |

| Image                                                                               | Code                   | Name                                                                | Quantity in device |
|-------------------------------------------------------------------------------------|------------------------|---------------------------------------------------------------------|--------------------|
|    | <a href="#">373393</a> | FIXED WHEEL B-VPP 160R-SG<br>(valid from 03/05/2025)                | 2.0 Each           |
|    | <a href="#">373396</a> | FIXED WHEEL B-VPP 200R-SG- 763618<br>(valid from 03/05/2025)        | 2.0 Each           |
|    | <a href="#">373399</a> | WHEEL, FIXED-BX-POEV 160XR-SG-<br>844626<br>(valid from 03/05/2025) | 2.0 Each           |
|    | <a href="#">372991</a> | Fixed castor BX-POEV 160KD-SG<br>(valid from 03/05/2025)            | 2.0 Each           |
|  | <a href="#">373402</a> | Fixed castor BX-POEV 200XR-SG-844630<br>(valid from 03/05/2025)     | 2.0 Each           |
|                                                                                     | <a href="#">146801</a> | FIXED WHEEL BX-POEV 200KD-SG<br>(valid from 03/05/2025)             | 2.0 Each           |
|  | <a href="#">372993</a> | Swivel castor LEX-POEV 160KD-SG-IS<br>(valid from 03/05/2025)       | 2.0 Each           |
|                                                                                     | <a href="#">373277</a> | (valid from 03/05/2025)                                             | 2.0 Each           |
|                                                                                     | <a href="#">373279</a> | (valid from 03/05/2025)                                             | 2.0 Each           |
|                                                                                     | <a href="#">373280</a> | (valid from 03/05/2025)                                             | 2.0 Each           |
|  | <a href="#">367443</a> | CNS direction locking system RI-03.03-KX<br>(valid from 03/05/2025) | 2.0 Each           |
|  | <a href="#">83144</a>  | WASHER, BACKING A 8,4DIN 9021<br>1.4301<br>(valid from 03/05/2025)  | 16.0 Each          |

| Image                                                                               | Code                   | Name                                                            | Quantity in device |
|-------------------------------------------------------------------------------------|------------------------|-----------------------------------------------------------------|--------------------|
|    | <a href="#">81098</a>  | Hexagon screw ISO 4017-M8x25<br>(valid from 03/05/2025)         | 16.0 Each          |
|    | <a href="#">372911</a> | body for push handle holder<br>(valid from 03/05/2025)          | 2.0 Each           |
|    | <a href="#">350519</a> | Tube D28x1-489 Form A<br>(valid from 03/05/2025)                | 1.0 Each           |
|                                                                                     | <a href="#">372912</a> | Cover push handle holder right, logo<br>(valid from 03/05/2025) | 1.0 Each           |
|    | <a href="#">372913</a> | Cover push handle holder left, logo<br>(valid from 03/05/2025)  | 1.0 Each           |
|  | <a href="#">83031</a>  | washer A 8.4 DIN 125 brass<br>(valid from 03/05/2025)           | 8.0 Each           |
|  | <a href="#">284979</a> | door lock 2074-U111-IA<br>(valid from 03/05/2025)               | 2.0 Each           |
|  | <a href="#">355603</a> | Stop<br>(valid from 03/05/2025)                                 | 2.0 Each           |
|  | <a href="#">147251</a> | SPRING,PRESSURE- VD 162<br>(valid from 03/05/2025)              | 1.0 Each           |
|  | <a href="#">377863</a> | Door lock cpl.<br>(valid from 03/05/2025)                       | 2.0 Each           |

| Image                                                                               | Code                   | Name                                                                | Quantity in device |
|-------------------------------------------------------------------------------------|------------------------|---------------------------------------------------------------------|--------------------|
|    | <a href="#">291568</a> | Locking pin POM C black<br>(valid from 03/05/2025)                  | 1.0 Each           |
|    | <a href="#">291534</a> | Mushroom handle w.thread M5, l.150/25 M5<br>(valid from 03/05/2025) | 1.0 Each           |
|    | <a href="#">291567</a> | Pressure spring D11x1-26<br>(valid from 03/05/2025)                 | 1.0 Each           |
|   | <a href="#">127765</a> | Grounding strap<br>(valid from 03/05/2025)                          | 1.0 Each           |
|  | <a href="#">71129</a>  | Right side spring T-19524R<br>(valid from 03/05/2025)               | 2.0 Each           |
|  | <a href="#">71128</a>  | Pressure spring VD-155A-10<br>(valid from 03/05/2025)               | 1.0 Each           |
|  | <a href="#">378943</a> | Safety flap cpl.<br>(valid from 03/05/2025)                         | 1.0 Each           |
|  | <a href="#">291378</a> | plastic cover for magnet<br>(valid from 03/05/2025)                 | 1.0 Each           |