

Sparepart documentation

Kein Bild

[TTW 24 EN PK DZE](#)

Prod. No.: 390255

Product details:

Tray transport trolley, for passive cooling with eutectic plates
2 compartments
Capacity: 24 Euronorm trays
insertion: lengthwise
Space between ledges: 115 mm

Spareparts


Image	Code	Name	Quantity in device
	144098	Rubber buffer 12.5 rd form 2492 (valid from 02/19/2025)	39.0 Each
	350498	Corpus hinge right cpl., passivated (valid from 02/19/2025)	1.0 Each
	350496	Corpus hinge left cpl., passivated (valid from 02/19/2025)	1.0 Each
	373056	Corner bumper bottom part (valid from 02/19/2025)	1.0 Each
	372932	Corner bumper both sides open (valid from 02/19/2025)	1.0 Each
	372933	Bumper corner open on one side left (valid from 02/19/2025)	1.0 Each
	372934	Bumper corner open on one side right (valid from 02/19/2025)	1.0 Each

Image	Code	Name	Quantity in device
	359327	Insert for impact bar (valid from 02/19/2025)	4.0 Each
	291374	Bumper Re-front, Li-rear (valid from 02/19/2025)	1.0 Each
	387796	Plug SFL14 (valid from 02/19/2025)	2.0 Each
	291375	(valid from 02/19/2025)	1.0 Each
	284998	Plastic locking (valid from 02/19/2025)	1.0 Each
	376576	Door handle right - without lock (valid from 02/19/2025)	1.0 Each
	291538	(valid from 02/19/2025)	1.0 Each
	284288	Insert for door lock, not lockable (valid from 02/19/2025)	1.0 Each
	389922	Lock - plastic, left (valid from 02/19/2025)	1.0 Each
	70914	Allen screw ISO 7380 M5x8 A2 m. Fl. (valid from 02/19/2025)	4.0 Each
	291302	Bumper upper-front (valid from 02/19/2025)	1.0 Each
	291303	(valid from 02/19/2025)	1.0 Each
	291304	(valid from 02/19/2025)	1.0 Each
	291307	Bumper upper-rear (valid from 02/19/2025)	1.0 Each
	384218	Corpus hinge right, bottom cpl., TTW H1 (valid from 02/19/2025)	1.0 Each
	384219	Corpus hinge left, bottom cpl., TTW H1 (valid from 02/19/2025)	1.0 Each
	384213	(valid from 02/19/2025)	1.0 Each


Image	Code	Name	Quantity in device
	<u>384212</u>	(valid from 02/19/2025)	1.0 Each
	<u>373392</u>	Castor wheel with brake LE-VPP160R-FI-SG (valid from 02/19/2025)	2.0 Each
	<u>373391</u>	Castor wheel LE-VPP 160R-SG (valid from 02/19/2025)	2.0 Each
	<u>373395</u>	CASTER WHEEL LE-VPP 200R-FI-SG (valid from 02/19/2025)	2.0 Each
	<u>373394</u>	CASTER WHEEL LE-VPP 200R-SG (valid from 02/19/2025)	2.0 Each
	<u>373398</u>	Swivel castor LEX-POEV 160XR-SG-FI-84462 (valid from 02/19/2025)	2.0 Each
	<u>373397</u>	Swivel castor LEX-POEV 160XR-SG-844624 (valid from 02/19/2025)	2.0 Each
	<u>373401</u>	WHEEL, CASTER LEX-POEV 200XR-SG-844629 (valid from 02/19/2025)	2.0 Each
	<u>373400</u>	WHEEL, CASTER-LEX-POEV 200XR-SG-844628 (valid from 02/19/2025)	2.0 Each
	<u>291431</u>	Swivel castorLEX-POEV 200XR-IS-SG-867787 (valid from 02/19/2025)	2.0 Each


Image	Code	Name	Quantity in device
	373393	FIXED WHEEL B-VPP 160R-SG (valid from 02/19/2025)	2.0 Each
	373396	FIXED WHEEL B-VPP 200R-SG- 763618 (valid from 02/19/2025)	2.0 Each
	373399	WHEEL, FIXED-BX-POEV 160XR-SG- 844626 (valid from 02/19/2025)	2.0 Each
	372991	Fixed castor BX-POEV 160KD-SG (valid from 02/19/2025)	2.0 Each
	373402	Fixed castor BX-POEV 200XR-SG-844630 (valid from 02/19/2025)	2.0 Each
	146801	FIXED WHEEL BX-POEV 200KD-SG (valid from 02/19/2025)	2.0 Each
	372993	Swivel castor LEX-POEV 160KD-SG-IS (valid from 02/19/2025)	2.0 Each
	373277	(valid from 02/19/2025)	2.0 Each
	373279	(valid from 02/19/2025)	2.0 Each
	373280	(valid from 02/19/2025)	2.0 Each
	367443	CNS direction locking system RI-03.03-KX (valid from 02/19/2025)	2.0 Each
	83144	WASHER,BACKING A 8,4DIN 9021 1.4301 (valid from 02/19/2025)	16.0 Each





Image	Code	Name	Quantity in device
	<u>81098</u>	Hexagon screw ISO 4017-M8x25 (valid from 02/19/2025)	16.0 Each
	<u>372911</u>	body for push handle holder (valid from 02/19/2025)	2.0 Each
	<u>350519</u>	Tube D28x1-489 Form A (valid from 02/19/2025)	1.0 Each
	<u>372912</u>	Cover push handle holder right, logo (valid from 02/19/2025)	1.0 Each
	<u>372913</u>	Cover push handle holder left, logo (valid from 02/19/2025)	1.0 Each
	<u>83031</u>	washer A 8.4 DIN 125 brass (valid from 02/19/2025)	8.0 Each
	<u>284979</u>	door lock 2074-U111-IA (valid from 02/19/2025)	2.0 Each
	<u>355603</u>	Stop (valid from 02/19/2025)	2.0 Each
	<u>147251</u>	SPRING,PRESSURE- VD 162 (valid from 02/19/2025)	1.0 Each
	<u>377863</u>	Door lock cpl. (valid from 02/19/2025)	2.0 Each

Image	Code	Name	Quantity in device
	291568	Locking pin POM C black (valid from 02/19/2025)	1.0 Each
	291534	Mushroom handle w.thread M5, l.150/25 M5 (valid from 02/19/2025)	1.0 Each
	291567	Pressure spring D11x1-26 (valid from 02/19/2025)	1.0 Each
	127765	Grounding strap (valid from 02/19/2025)	1.0 Each
	71129	Right side spring T-19524R (valid from 02/19/2025)	2.0 Each
	71128	Pressure spring VD-155A-10 (valid from 02/19/2025)	1.0 Each
	378943	Safety flap cpl. (valid from 02/19/2025)	1.0 Each
	291378	plastic cover for magnet (valid from 02/19/2025)	1.0 Each