

# Sparepart documentation





## BC classic 3.1 BHG-I


**Prod. No.:** 574406

### **Product details:**

COOK classic<br>For 3 COOK table-top units<br>Device placement niche: 1211 x 648 x 300 mm<br>basic model 380236<br><br>Rating /connection load:<br>3 x 230 V Schuko socket outlets,<br>3 x 400 V CEE socket outlets (max. 20 kW)<br>32 A CEE plug<br>400 V, 50/60 Hz, 3N PE, 20.8 kW





### Spareparts



| Image                                                                               | Code                   | Name                                                                | Quantity in device |
|-------------------------------------------------------------------------------------|------------------------|---------------------------------------------------------------------|--------------------|
|                                                                                     | <a href="#">144131</a> | rubber buffer 21rd x 15,5 black<br>(valid from 03/15/2018)          | 1.0 Each           |
|    | <a href="#">375583</a> | Magnet QA-40x20x5-NI-N52<br>(valid from 03/15/2018)                 | 1.0 Each           |
|  | <a href="#">145793</a> | PLUG, 40 X 40 POLY. BLACK<br>(valid from 03/15/2018)                | 1.0 Each           |
|  | <a href="#">105673</a> | lip DA 200-10<br>(valid from 03/15/2018)                            | 3.0 Each           |
|  | <a href="#">375549</a> | Stop screw M6 x 10<br>(valid from 03/15/2018)                       | 9.0 Each           |
|                                                                                     | <a href="#">375488</a> | Profile with sealing lip<br>(valid from 03/15/2018)                 | 2.485 Meter        |
|  | <a href="#">385096</a> | Seal 9x5,5 black<br>(valid from 02/05/2020)                         | 1.0 Meter          |
|  | <a href="#">146330</a> | Shell-type handle s. RAL7012 basalt gray<br>(valid from 03/15/2018) | 2.0 Each           |
|  | <a href="#">107474</a> | Harness BC FS 2.1 fan<br>(valid from 01/13/2023)                    | 1.0 Each           |

| Image                                                                               | Code                          | Name                                                                | Quantity in device |
|-------------------------------------------------------------------------------------|-------------------------------|---------------------------------------------------------------------|--------------------|
|    | <a href="#"><u>380287</u></a> | Fan tray complete BC FS X.1<br>(valid from 03/15/2018)              | 2.0 Each           |
|    | <a href="#"><u>106820</u></a> | Radial fan Typ Papst D2E146-HT79-32<br>(valid from 03/15/2018)      | 1.0 Each           |
|    | <a href="#"><u>106852</u></a> | Protective grid cable side<br>(valid from 03/15/2018)               | 1.0 Each           |
|    | <a href="#"><u>106853</u></a> | Protective grid on opposite side<br>(valid from 03/15/2018)         | 1.0 Each           |
|                                                                                     | <a href="#"><u>380608</u></a> | Fan guard<br>(valid from 03/15/2018)                                | 1.0 Each           |
|                                                                                     | <a href="#"><u>81320</u></a>  | Tapping screw ISO7051-ST4,2x19<br>(valid from 03/15/2018)           | 4.0 Each           |
|   | <a href="#"><u>146708</u></a> | Bow-type handle CNS 128mm<br>(valid from 03/15/2018)                | 1.0 Each           |
|  | <a href="#"><u>105194</u></a> | fixing clamp H3P-N66-NA<br>(valid from 03/15/2018)                  | 1.0 Each           |
|  | <a href="#"><u>106895</u></a> | label "Don't spray with water"<br>(valid from 03/15/2018)           | 1.0 Each           |
|                                                                                     | <a href="#"><u>380586</u></a> | Sound insulation mat, one-sided self-adh<br>(valid from 03/15/2018) | 2.0 Each           |
|                                                                                     | <a href="#"><u>382738</u></a> | Revision panel cpl. with lock<br>(valid from 03/15/2018)            | 2.0 Each           |
|  | <a href="#"><u>342731</u></a> | Gasket profile-5134 gray MP<br>(valid from 03/15/2018)              | 4.2 Meter          |
|  | <a href="#"><u>375584</u></a> | fastening complete BC FS<br>(valid from 03/15/2018)                 | 2.0 Each           |

| Image                                                                               | Code                          | Name                                                                         | Quantity in device |
|-------------------------------------------------------------------------------------|-------------------------------|------------------------------------------------------------------------------|--------------------|
|    | <a href="#"><u>376314</u></a> | open handheld pa black<br>(valid from 03/15/2018)                            | 2.0 Each           |
|    | <a href="#"><u>375556</u></a> | Splash guard ESG BC FS 3<br>(valid from 03/15/2018)                          | 1.0 Each           |
|    | <a href="#"><u>384537</u></a> | Lightning 2x1/1<br>(valid from 09/17/2024)                                   | 1.0 Each           |
|    | <a href="#"><u>388167</u></a> | Lightning module cpl. BC classic 3<br>(valid from 02/15/2024)                | 1.0 Each           |
|    | <a href="#"><u>376367</u></a> | Filter Blind cpl. for BC FS<br>(valid from 03/15/2018)                       | 1.0 Each           |
|    | <a href="#"><u>380657</u></a> | Filter cpl. for BC FS<br>(valid from 03/15/2018)                             | 6.0 Each           |
|  | <a href="#"><u>106874</u></a> | Connecting cable H07RN-F 5x4mm <sup>2</sup> /4,5m<br>(valid from 03/15/2018) | 1.0 Each           |
|  | <a href="#"><u>106865</u></a> | socket CEE 5x16A<br>(valid from 03/15/2018)                                  | 3.0 Each           |
|  | <a href="#"><u>106708</u></a> | magnetic switch MK4-1A75-C-300W<br>(valid from 03/15/2018)                   | 2.0 Each           |
|  | <a href="#"><u>107141</u></a> | Installation contactor ESB40-40-230AC/DC<br>(valid from 03/15/2018)          | 1.0 Each           |
|  | <a href="#"><u>107429</u></a> | Circuit breaker ABB 3x16A-B S 203-B 16<br>(valid from 03/15/2018)            | 3.0 Each           |
|  | <a href="#"><u>107143</u></a> | Circuit breaker ABB S 201-B 10A<br>(valid from 03/15/2018)                   | 1.0 Each           |

| Image                                                                               | Code                          | Name                                                                | Quantity in device |
|-------------------------------------------------------------------------------------|-------------------------------|---------------------------------------------------------------------|--------------------|
|                                                                                     | <a href="#"><u>107184</u></a> | ECB-terminal 741PE<br>(valid from 03/15/2018)                       | 1.0 Each           |
|    | <a href="#"><u>107180</u></a> | Mains supply terminal 5 pole 25mm²<br>(valid from 03/15/2018)       | 1.0 Each           |
|                                                                                     | <a href="#"><u>107478</u></a> | Folding window IP66 for 12 units<br>(valid from 03/15/2018)         | 2.0 Each           |
|    | <a href="#"><u>149563</u></a> | PTC sensor StörkTronic TF-PTC No. 195040<br>(valid from 03/15/2018) | 2.0 Each           |
|    | <a href="#"><u>107493</u></a> | Control unit BC FS x.1<br>(valid from 03/15/2018)                   | 1.0 Each           |
|                                                                                     | <a href="#"><u>375574</u></a> | Sealing frame for control unit BS FS<br>(valid from 03/15/2018)     | 1.0 Each           |
|   | <a href="#"><u>106311</u></a> | Hexagon nut M20x1.5 (plastic)<br>(valid from 03/15/2018)            | 6.0 Each           |
|  | <a href="#"><u>106304</u></a> | Cable gland M20x1.5 black<br>(valid from 03/15/2018)                | 2.0 Each           |
|  | <a href="#"><u>107670</u></a> | safety socket swiss version T25<br>(valid from 03/15/2018)          | 2.0 Each           |
|  | <a href="#"><u>106891</u></a> | seal for ABL electrical outlets<br>(valid from 03/15/2018)          | 2.0 Each           |
|  | <a href="#"><u>107554</u></a> | Socket Typ 1661060<br>(valid from 03/15/2018)                       | 3.0 Each           |
|  | <a href="#"><u>107716</u></a> | Socket outlet protective contact-black<br>(valid from 05/03/2022)   | 1.0 Each           |

| Image                                                                               | Code                          | Name                                                                | Quantity in device |
|-------------------------------------------------------------------------------------|-------------------------------|---------------------------------------------------------------------|--------------------|
|    | <a href="#"><u>107514</u></a> | LED converter univer. 20W BI; 350-700mA<br>(valid from 03/15/2018)  | 1.0 Each           |
|    | <a href="#"><u>107249</u></a> | Line filter FN2010-6-06<br>(valid from 03/15/2018)                  | 1.0 Each           |
|    | <a href="#"><u>107568</u></a> | High voltage power Supply HV-D<br>(valid from 04/06/2023)           | 1.0 Each           |
|                                                                                     | <a href="#"><u>388671</u></a> | Mounting sheet Trafo kpl.<br>(valid from 08/19/2025)                | 1.0 Each           |
|                                                                                     | <a href="#"><u>107472</u></a> | High voltage contact ceramic<br>(valid from 03/15/2018)             | 4.0 Each           |
|                                                                                     | <a href="#"><u>121642</u></a> | Contacting spring incl. screw VA<br>(valid from 08/11/2023)         | 2.0 Each           |
|   | <a href="#"><u>380587</u></a> | Iontec filter element 2.0 left cpl.<br>(valid from 03/15/2018)      | 1.0 Each           |
|                                                                                     | <a href="#"><u>134216</u></a> | IonTec filter left replacement f. 380587<br>(valid from 10/05/2023) | 1.0 Each           |
|  | <a href="#"><u>384673</u></a> | Iontec filter element 470 cpl. left<br>(valid from 04/06/2023)      | 1.0 Each           |
|  | <a href="#"><u>107276</u></a> | Sticker warning of el. Voltage<br>(valid from 03/15/2018)           | 1.0 Each           |
|  | <a href="#"><u>380588</u></a> | Iontec filter element 2.0 right cpl.<br>(valid from 03/15/2018)     | 1.0 Each           |
|                                                                                     | <a href="#"><u>134217</u></a> | IonTec filter right replacement f 380587<br>(valid from 10/05/2023) | 1.0 Each           |
|  | <a href="#"><u>386542</u></a> | Iontec filter element 470 cpl. right<br>(valid from 04/06/2023)     | 1.0 Each           |
|  | <a href="#"><u>134046</u></a> | Activated carbon foam Set/2pc BC classic<br>(valid from 11/27/2019) | 1.0 Each           |

| Image                                                                               | Code                          | Name                                                              | Quantity in device |
|-------------------------------------------------------------------------------------|-------------------------------|-------------------------------------------------------------------|--------------------|
|    | <a href="#"><u>380270</u></a> | Expanded metal filter<br>(valid from 03/15/2018)                  | 2.0 Each           |
|    | <a href="#"><u>107213</u></a> | synthetic filter 595 x 235 x 20 mm<br>(valid from 03/15/2018)     | 2.0 Each           |
|                                                                                     | <a href="#"><u>121802</u></a> | Filter set BC classic .1 for one year<br>(valid from 03/15/2018)  | 1.0 Each           |
|    | <a href="#"><u>106896</u></a> | label "Unplug before opening"<br>(valid from 03/15/2018)          | 2.0 Each           |
|    | <a href="#"><u>370493</u></a> | SCREW,STOP M6X6 DIN 923<br>(valid from 03/15/2018)                | 4.0 Each           |
|                                                                                     | <a href="#"><u>375726</u></a> | Right tube for gallery BC FS<br>(valid from 03/15/2018)           | 1.0 Each           |
|                                                                                     | <a href="#"><u>375727</u></a> | Left tube for gallery BC FS<br>(valid from 03/15/2018)            | 1.0 Each           |
|  | <a href="#"><u>375731</u></a> | Base galery<br>(valid from 03/15/2018)                            | 10.0 Each          |
|                                                                                     | <a href="#"><u>375729</u></a> | Pipe middle for gallery BC FS 3<br>(valid from 03/15/2018)        | 1.0 Each           |
|  | <a href="#"><u>370687</u></a> | Cast. whl. double 75 lock. plate 77x67<br>(valid from 03/15/2018) | 2.0 Each           |
|  | <a href="#"><u>370688</u></a> | Cast. whl. double 75 plate 77x67<br>(valid from 03/15/2018)       | 6.0 Each           |
|  | <a href="#"><u>81098</u></a>  | Hexagon screw ISO 4017-M8x25<br>(valid from 03/15/2018)           | 32.0 Each          |