

Sparepart documentation



BPT E 2 x 36 duo H/H banquet

Prod. No.: 575214

Product details:

B.PROTHERM E 2 x 36 x 2/1 duo heated/heated banquet
B. PROTHERM E food transport container 2/1, convection-heated
Made of corrosion-resistant steel, with hinged doors, mobile.
2 x 36 pairs of support ledges
Space between ledges: 38.3 mm
left compartment: convection-heated,
right compartment: convection-heated,
temperature range adjustable between +30 °C and +90 °C.
Mains frequency: 50/60 Hz

Basic model: 386619

Spareparts



Image	Code	Name	Quantity in device
	388087	Insert (valid from 02/15/2022)	2.0 Each
	388136	Mounting bracket 80° (valid from 02/15/2022)	2.0 Each
	386649	Corpus hinge top right (valid from 02/15/2022)	1.0 Each
	374840	Rubber buffer D25xh12-d5 (valid from 02/15/2022)	2.0 Each
	386786	Tube D28x1 L=586,4 (valid from 02/15/2022)	1.0 Each
	372911	body for push handle holder (valid from 02/15/2022)	2.0 Each
	372913	Cover push handle holder left, logo (valid from 02/15/2022)	1.0 Each
	372912	Cover push handle holder right, logo (valid from 02/15/2022)	1.0 Each



Image	Code	Name	Quantity in device
	<u>386652</u>	Hinge (valid from 02/15/2022)	2.0 Each
	<u>83031</u>	washer A 8.4 DIN 125 brass (valid from 02/15/2022)	2.0 Each
	<u>387304</u>	Warm module cpl. 1450W (valid from 04/18/2023)	2.0 Each
	<u>107469</u>	Radial Fan R2K150/0020-4218 (valid from 02/15/2022)	1.0 Each
	<u>388233</u>	Spring 6,9x8 VD_063H_20_1 (valid from 11/02/2022)	1.0 Each
	<u>107671</u>	Tubular heater 1450W 20.43035.020 (valid from 02/15/2022)	1.0 Each
	<u>107694</u>	Temperature sensor PT1000_B. PROTHERM (valid from 02/15/2022)	1.0 Each
	<u>105805</u>	Safety temperature limiter 135 °C (valid from 02/15/2022)	1.0 Each
	<u>105194</u>	fixing clamp H3P-N66-NA (valid from 02/15/2022)	1.0 Each




Image	Code	Name	Quantity in device
	386579	mold without lock <i>(valid from 02/15/2022)</i>	1.0 Each
	386767	Push Rod 36 <i>(valid from 02/15/2022)</i>	1.0 Each
	388138	Knob cpl. <i>(valid from 02/15/2022)</i>	1.0 Each
	386565	Door handle <i>(valid from 02/15/2022)</i>	1.0 Each
	387941	Emergency opening <i>(valid from 03/11/2026)</i>	1.0 Each



Image	Code	Name	Quantity in device
	377734	Pressure spring VD-180-07 (valid from 08/03/2022)	2.0 Each
	386562	Cover (valid from 02/15/2022)	1.0 Each
	389058	Bushing (valid from 02/15/2022)	1.0 Each
	386778	Seal (valid from 02/15/2022)	4.005 Meter
	387946	Emergency opening left (valid from 02/15/2022)	1.0 Each
	386547	Display Mount (valid from 02/21/2022)	2.0 Each
	107664	BPT Display (valid from 02/21/2022)	2.0 Each
	386476	Display Foil Atlas (valid from 02/21/2022)	2.0 Each
	369654	Plug holder universal (valid from 02/21/2022)	1.0 Each
	117766	plastic cover ring for plug holder (valid from 02/15/2022)	1.0 Each
	105429	terminal block Wieland KL 24/3 SL (valid from 02/21/2022)	2.0 Each
	107722	BPT Power PCB (valid from 02/21/2022)	2.0 Each
	106304	Cable gland M20x1.5 black (valid from 02/21/2022)	1.0 Each

Image	Code	Name	Quantity in device
	<u>106311</u>	Hexagon nut M20x1.5 (plastic) (valid from 02/21/2022)	1.0 Each
	<u>106708</u>	magnetic switch MK4-1A75-C-300W (valid from 02/21/2022)	2.0 Each
	<u>107692</u>	Decal equipotential bonding (valid from 02/21/2022)	1.0 Each
	<u>107682</u>	Spiral cable Europe 3x1,5 qmm BL-570 (valid from 05/23/2022)	1.0 Each
	<u>373391</u>	Castor wheel LE-VPP 160R-SG (valid from 02/15/2022)	2.0 Each
	<u>373392</u>	Castor wheel with brake LE-VPP160R-FI-SG (valid from 02/15/2022)	2.0 Each