

Sparepart documentation



BPT E 2 x 30 (24) duo H/C

Prod. No.: 386616

Product details:

B.PROTHERM E 2 x 30 (24) x 1/1 duo heated/cooled
B. PROTHERM E food transport container 1/1, convection-heated /convection-cooled
Made of corrosion-resistant steel, with hinged doors, mobile.
left compartment: convection-heated, temperature range adjustable between +30 °C and +95 °C,
30 pairs of support ledges
right compartment: convection-cooled, temperature range adjustable between +2 °C and +10 °C,
30 pairs of support ledges with 24 x 1/1 and 6 x 1/2
Refrigerant: propane R290.
Mains frequency: 50/60 Hz

Spareparts







Image	Code	Name	Quantity in device
	388087	Insert (valid from 05/11/2022)	2.0 Each
	388101	Comfort opening right without drawbar (valid from 05/11/2022)	1.0 Each
	144218	PLUG-LAMINATE- 40X40X1,25 SERIES 120 (valid from 09/07/2022)	2.0 Each
	83031	washer A 8.4 DIN 125 brass (valid from 09/07/2022)	3.0 Each
	388103	Comfort opening left (valid from 05/11/2022)	1.0 Each
	386646	Spring VD-165 (valid from 07/28/2022)	1.0 Each
	246508	Pressure spring D-180-03 FA. GUTEKUNST (valid from 07/28/2022)	2.0 Each
	388136	Mounting bracket 80° (valid from 05/11/2022)	2.0 Each








Image	Code	Name	Quantity in device
	<u>386649</u>	Corpus hinge top right (valid from 05/11/2022)	1.0 Each
	<u>386650</u>	Corpus hinge top left (valid from 05/11/2022)	1.0 Each
	<u>386724</u>	Filter (valid from 05/11/2022)	1.0 Each
	<u>374840</u>	Rubber buffer D25xh12-d5 (valid from 05/11/2022)	2.0 Each
	<u>386786</u>	Tube D28x1 L=586,4 (valid from 05/11/2022)	1.0 Each
	<u>372911</u>	body for push handle holder (valid from 05/11/2022)	2.0 Each
	<u>372913</u>	Cover push handle holder left, logo (valid from 05/11/2022)	1.0 Each
	<u>372912</u>	Cover push handle holder right, logo (valid from 05/11/2022)	1.0 Each
	<u>386652</u>	Hinge (valid from 05/11/2022)	2.0 Each










Image	Code	Name	Quantity in device
	387165	Warm module cpl. 950 W (valid from 05/11/2022)	1.0 Each
	107469	Radial Fan R2K150/0020-4218 (valid from 05/11/2022)	1.0 Each
	388233	Spring 6,9x8 VD_063H_20_1 (valid from 11/02/2022)	1.0 Each
	107672	Tubular heater 950W 20.43035.010 (valid from 05/11/2022)	1.0 Each
	107694	Temperature sensor PT1000_B. PROTHERM (valid from 05/11/2022)	1.0 Each
	105805	Safety temperature limiter 135 °C (valid from 05/11/2022)	1.0 Each
	149200	Axial fan 4656 ZWU 230VAC (valid from 05/11/2022)	1.0 Each
	134246	Condenser Fan of Cooling Modul with R290 (valid from 03/19/2024)	1.0 Each
	149785	Condenser Fan of Cooling Modul with R290 (valid from 05/11/2022)	1.0 Each
	386715	Condensate pan cpl. (valid from 05/11/2022)	1.0 Each





Image	Code	Name	Quantity in device
	386579	mold without lock (valid from 05/11/2022)	1.0 Each
	386581	mold with lock (valid from 05/11/2022)	1.0 Each
	386673	Lock (valid from 05/11/2022)	1.0 Each
	70914	Allen screw ISO 7380 M5x8 A2 m. Fl. (valid from 05/11/2022)	1.0 Each
	386903	Key (valid from 05/11/2022)	2.0 Each







Image	Code	Name	Quantity in device
	386766	Push Rod 30 (valid from 05/11/2022)	1.0 Each
	386771	Spring cpl. (valid from 11/29/2022)	1.0 Each
	388138	Knob cpl. (valid from 05/11/2022)	1.0 Each
	386565	Door handle (valid from 05/11/2022)	1.0 Each
	387941	Emergency opening (valid from 12/02/2024)	1.0 Each
	377734	Pressure spring VD-180-07 (valid from 08/03/2022)	2.0 Each
	386562	Cover (valid from 05/11/2022)	1.0 Each
	389058	Bushing (valid from 05/11/2022)	1.0 Each












Image	Code	Name	Quantity in device
	386778	Seal (valid from 05/11/2022)	3.188 Meter
	387946	Emergency opening left (valid from 12/02/2024)	1.0 Each
	389005	Ventilation flap (valid from 08/09/2024)	1.0 Each
	365428	O-RING, 67.00 X 1.50 EPDM70 (valid from 05/11/2022)	1.0 Each
	386580	Retaining tube for ventilation flap (valid from 05/11/2022)	1.0 Each
	386547	Display Mount (valid from 05/16/2022)	2.0 Each
	107664	BPT Display (valid from 05/16/2022)	2.0 Each
	386476	Display Foil Atlas (valid from 05/16/2022)	2.0 Each
	369654	Plug holder universal (valid from 05/16/2022)	1.0 Each
	117766	plastic cover ring for plug holder (valid from 05/11/2022)	1.0 Each
	105429	terminal block Wieland KL 24/3 SL (valid from 05/16/2022)	2.0 Each
	107722	BPT Power PCB (valid from 05/16/2022)	1.0 Each












Image	Code	Name	Quantity in device
	<u>106304</u>	Cable gland M20x1.5 black (valid from 05/16/2022)	1.0 Each
	<u>106311</u>	Hexagon nut M20x1.5 (plastic) (valid from 05/16/2022)	1.0 Each
	<u>106708</u>	magnetic switch MK4-1A75-C-300W (valid from 05/16/2022)	2.0 Each
	<u>107692</u>	Decal equipotential bonding (valid from 05/16/2022)	1.0 Each
	<u>107682</u>	Spiral cable Europe 3x1,5 qmm BL-570 (valid from 05/23/2022)	1.0 Each
	<u>107683</u>	Spiral cable UK 3x1,5 qmm BL-570 (13A) (valid from 05/16/2022)	1.0 Each
	<u>107684</u>	Spiral cable CH 3x1,5 qmm BL-570 (10A) (valid from 05/16/2022)	1.0 Each
	<u>107687</u>	Spiral cable AUS 3x1,5 qmm B-570 10A (valid from 05/16/2022)	1.0 Each
	<u>107689</u>	Spiral cable Denmark 3x1,5 qmm B-570 13A (valid from 05/16/2022)	1.0 Each
	<u>107715</u>	Protective-socket Swiss-Standard T13 bla (valid from 05/16/2022)	1.0 Each

Image	Code	Name	Quantity in device
	106803	Build-in socket British standard (valid from 05/16/2022)	1.0 Each
	106822	Safety socket Denmark (valid from 05/16/2022)	1.0 Each
	106737	Build-in socket with pin (valid from 05/16/2022)	1.0 Each
	107716	Socket outlet protective contact-black (valid from 05/16/2022)	1.0 Each
	106891	seal for ABL electrical outlets (valid from 05/16/2022)	1.0 Each
	373397	Swivel castor LEX-POEV 160XR-SG-844624 (valid from 05/11/2022)	2.0 Each
	373398	Swivel castor LEX-POEV 160XR-SG-FI-84462 (valid from 05/11/2022)	2.0 Each
	373399	WHEEL, FIXED-BX-POEV 160XR-SG-844626 (valid from 05/11/2022)	2.0 Each
	373393	FIXED WHEEL B-VPP 160R-SG (valid from 05/11/2022)	2.0 Each
	373394	CASTER WHEEL LE-VPP 200R-SG (valid from 05/11/2022)	2.0 Each

Image	Code	Name	Quantity in device
	<u>373395</u>	CASTER WHEEL LE-VPP 200R-FI-SG (valid from 05/11/2022)	2.0 Each
	<u>373396</u>	FIXED WHEEL B-VPP 200R-SG- 763618 (valid from 05/11/2022)	2.0 Each
	<u>373400</u>	WHEEL, CASTER-LEX-POEV 200XR-SG- 844628 (valid from 05/11/2022)	2.0 Each
	<u>373401</u>	WHEEL, CASTER LEX-POEV 200XR-SG- 844629 (valid from 05/11/2022)	2.0 Each
	<u>373402</u>	Fixed castor BX-POEV 200XR-SG-844630 (valid from 05/11/2022)	2.0 Each
	<u>373391</u>	Castor wheel LE-VPP 160R-SG (valid from 05/11/2022)	2.0 Each
	<u>373392</u>	Castor wheel with brake LE-VPP160R-FI-SG (valid from 05/11/2022)	2.0 Each
	<u>373593</u>	Swivel castor LE-POEV 160R-FI-SG 843898 (valid from 09/12/2022)	2.0 Each

Image	Code	Name	Quantity in device
	373594	Fixed castor B-POEV 160R-SG 843899 <i>(valid from 09/12/2022)</i>	2.0 Each