

# Sparepart documentation

## BPT E 12 H



**Prod. No.:** 386605








**Product details:**






B.PROTHERM E 12 x 1/1 heated<br>B.PROTHERM E food transport container 1/1, convection-heated<br>Made of corrosion-resistant steel, with hinged door, mobile.<br>12 pairs of support ledges<br>Space between ledges: 38.3 mm<br>Temperature range adjustable between +30 °C and +95°C<br>Mains frequency: 50/60 Hz<br>












### Spareparts









| Image | Code                   | Name                                                                 | Quantity in device |
|-------|------------------------|----------------------------------------------------------------------|--------------------|
|       | <a href="#">388087</a> | Insert<br>(valid from 01/31/2022)                                    | 1.0 Each           |
|       | <a href="#">386646</a> | Spring VD-165<br>(valid from 07/28/2022)                             | 1.0 Each           |
|       | <a href="#">246508</a> | Pressure spring D-180-03 FA.<br>GUTEKUNST<br>(valid from 07/28/2022) | 2.0 Each           |
|       | <a href="#">388101</a> | Comfort opening right without drawbar<br>(valid from 01/31/2022)     | 1.0 Each           |
|       | <a href="#">144218</a> | PLUG-LAMINATE- 40X40X1,25 SERIES 120<br>(valid from 09/07/2022)      | 2.0 Each           |
|       | <a href="#">83031</a>  | washer A 8.4 DIN 125 brass<br>(valid from 09/07/2022)                | 3.0 Each           |
|       | <a href="#">388136</a> | Mounting bracket 80°<br>(valid from 01/31/2022)                      | 1.0 Each           |
|       | <a href="#">386649</a> | Corpus hinge top right<br>(valid from 01/31/2022)                    | 1.0 Each           |

| Image                                                                               | Code                   | Name                                                            | Quantity in device |
|-------------------------------------------------------------------------------------|------------------------|-----------------------------------------------------------------|--------------------|
|    | <a href="#">374840</a> | Rubber buffer D25xh12-d5<br>(valid from 01/31/2022)             | 1.0 Each           |
|    | <a href="#">387315</a> | Tube D28x1 L=268<br>(valid from 01/31/2022)                     | 1.0 Each           |
|    | <a href="#">372911</a> | body for push handle holder<br>(valid from 01/31/2022)          | 2.0 Each           |
|    | <a href="#">372913</a> | Cover push handle holder left, logo<br>(valid from 01/31/2022)  | 1.0 Each           |
|                                                                                     | <a href="#">372912</a> | Cover push handle holder right, logo<br>(valid from 01/31/2022) | 1.0 Each           |
|   | <a href="#">386652</a> | Hinge<br>(valid from 01/31/2022)                                | 1.0 Each           |
|  | <a href="#">387303</a> | Warm module cpl. 760W<br>(valid from 01/31/2022)                | 1.0 Each           |
|  | <a href="#">107469</a> | Radial Fan R2K150/0020-4218<br>(valid from 01/31/2022)          | 1.0 Each           |
|                                                                                     | <a href="#">388233</a> | Spring 6,9x8 VD_063H_20_1<br>(valid from 11/02/2022)            | 1.0 Each           |










| Image                                                                               | Code                   | Name                                                                | Quantity in device |
|-------------------------------------------------------------------------------------|------------------------|---------------------------------------------------------------------|--------------------|
|    | <a href="#">107673</a> | Tubular heater 760W 20.43035.000<br>(valid from 01/31/2022)         | 1.0 Each           |
|    | <a href="#">107694</a> | Temperature sensor PT1000_B.<br>PROTHERM<br>(valid from 01/31/2022) | 1.0 Each           |
|    | <a href="#">105805</a> | Safety temperature limiter 135 °C<br>(valid from 01/31/2022)        | 1.0 Each           |
|    | <a href="#">386579</a> | mold without lock<br>(valid from 01/31/2022)                        | 1.0 Each           |
|   | <a href="#">386581</a> | mold with lock<br>(valid from 01/31/2022)                           | 1.0 Each           |
|                                                                                     | <a href="#">386673</a> | Lock<br>(valid from 01/31/2022)                                     | 1.0 Each           |
|  | <a href="#">70914</a>  | Allen screw ISO 7380 M5x8 A2 m. FI.<br>(valid from 01/31/2022)      | 1.0 Each           |
|  | <a href="#">386903</a> | Key<br>(valid from 01/31/2022)                                      | 2.0 Each           |

| Image                                                                               | Code                   | Name                                                        | Quantity in device |
|-------------------------------------------------------------------------------------|------------------------|-------------------------------------------------------------|--------------------|
|    | <a href="#">387186</a> | Push Rod 12<br><i>(valid from 01/31/2022)</i>               | 1.0 Each           |
|  | <a href="#">386771</a> | Spring cpl.<br><i>(valid from 11/28/2022)</i>               | 1.0 Each           |
|  | <a href="#">388138</a> | Knob cpl.<br><i>(valid from 01/31/2022)</i>                 | 1.0 Each           |
|  | <a href="#">386565</a> | Door handle<br><i>(valid from 01/31/2022)</i>               | 1.0 Each           |
|                                                                                     | <a href="#">387941</a> | Emergency opening<br><i>(valid from 12/02/2024)</i>         | 1.0 Each           |
|  | <a href="#">377734</a> | Pressure spring VD-180-07<br><i>(valid from 08/03/2022)</i> | 2.0 Each           |
|                                                                                     | <a href="#">386562</a> | Cover<br><i>(valid from 01/31/2022)</i>                     | 1.0 Each           |

| Image                                                                               | Code                   | Name                                                           | Quantity in device |
|-------------------------------------------------------------------------------------|------------------------|----------------------------------------------------------------|--------------------|
|    | <a href="#">389058</a> | Bushing<br>(valid from 01/31/2022)                             | 1.0 Each           |
|    | <a href="#">386778</a> | Seal<br>(valid from 01/31/2022)                                | 1.768 Meter        |
|    | <a href="#">389005</a> | Ventilation flap<br>(valid from 08/09/2024)                    | 1.0 Each           |
|    | <a href="#">365428</a> | O-RING, 67.00 X 1.50 EPDM70<br>(valid from 01/31/2022)         | 1.0 Each           |
|   | <a href="#">386580</a> | Retaining tube for ventilation flap<br>(valid from 01/31/2022) | 1.0 Each           |
|  | <a href="#">386547</a> | Display Mount<br>(valid from 01/31/2022)                       | 1.0 Each           |
|  | <a href="#">107664</a> | BPT Display<br>(valid from 01/31/2022)                         | 1.0 Each           |
|  | <a href="#">386476</a> | Display Foil Atlas<br>(valid from 01/31/2022)                  | 1.0 Each           |
|  | <a href="#">369654</a> | Plug holder universal<br>(valid from 01/31/2022)               | 1.0 Each           |
|  | <a href="#">117766</a> | plastic cover ring for plug holder<br>(valid from 01/31/2022)  | 1.0 Each           |
|  | <a href="#">105429</a> | terminal block Wieland KL 24/3 SL<br>(valid from 01/31/2022)   | 1.0 Each           |

| Image                                                                               | Code                          | Name                                                              | Quantity in device |
|-------------------------------------------------------------------------------------|-------------------------------|-------------------------------------------------------------------|--------------------|
|    | <a href="#"><u>107722</u></a> | BPT Power PCB<br>(valid from 01/31/2022)                          | 1.0 Each           |
|                                                                                     | <a href="#"><u>107666</u></a> | BPT Power PCB (max.)<br>(valid from 01/31/2022)                   | 1.0 Each           |
|    | <a href="#"><u>106304</u></a> | Cable gland M20x1.5 black<br>(valid from 01/31/2022)              | 1.0 Each           |
|    | <a href="#"><u>106311</u></a> | Hexagon nut M20x1.5 (plastic)<br>(valid from 01/31/2022)          | 1.0 Each           |
|    | <a href="#"><u>106708</u></a> | magnetic switch MK4-1A75-C-300W<br>(valid from 01/31/2022)        | 1.0 Each           |
|   | <a href="#"><u>107692</u></a> | Decal equipotential bonding<br>(valid from 01/31/2022)            | 1.0 Each           |
|  | <a href="#"><u>107682</u></a> | Spiral cable Europe 3x1,5 qmm BL-570<br>(valid from 05/23/2022)   | 1.0 Each           |
|  | <a href="#"><u>107683</u></a> | Spiral cable UK 3x1,5 qmm BL-570 (13A)<br>(valid from 01/31/2022) | 1.0 Each           |
|  | <a href="#"><u>107684</u></a> | Spiral cable CH 3x1,5 qmm BL-570 (10A)<br>(valid from 01/31/2022) | 1.0 Each           |
|  | <a href="#"><u>107687</u></a> | Spiral cable AUS 3x1,5 qmm B-570 10A<br>(valid from 01/31/2022)   | 1.0 Each           |

| Image                                                                               | Code                          | Name                                                                 | Quantity in device |
|-------------------------------------------------------------------------------------|-------------------------------|----------------------------------------------------------------------|--------------------|
|    | <a href="#"><u>107689</u></a> | Spiral cable Denmark 3x1,5 qmm B-570 13A<br>(valid from 01/31/2022)  | 1.0 Each           |
|    | <a href="#"><u>107715</u></a> | Protective-socket Swiss-Standard T13 bla<br>(valid from 01/31/2022)  | 1.0 Each           |
|    | <a href="#"><u>106803</u></a> | Build-in socket British standard<br>(valid from 01/31/2022)          | 1.0 Each           |
|    | <a href="#"><u>106822</u></a> | Safety socket Denmark<br>(valid from 01/31/2022)                     | 1.0 Each           |
|    | <a href="#"><u>106737</u></a> | Build-in socket with pin<br>(valid from 01/31/2022)                  | 1.0 Each           |
|  | <a href="#"><u>107716</u></a> | Socket outlet protective contact-black<br>(valid from 01/31/2022)    | 1.0 Each           |
|  | <a href="#"><u>106891</u></a> | seal for ABL electrical outlets<br>(valid from 01/31/2022)           | 1.0 Each           |
|  | <a href="#"><u>369185</u></a> | DOUBLE STR. CASTOR75 lock.boa.galv. steel<br>(valid from 01/31/2022) | 2.0 Each           |
|  | <a href="#"><u>369186</u></a> | DOUBLE STR. CASTOR 75 board galv. steel<br>(valid from 01/31/2022)   | 2.0 Each           |
|  | <a href="#"><u>386501</u></a> | Swivel castor 125 lock., DIN-PL (gray)<br>(valid from 01/31/2022)    | 2.0 Each           |

| Image                                                                               | Code                   | Name                                                                    | Quantity in device |
|-------------------------------------------------------------------------------------|------------------------|-------------------------------------------------------------------------|--------------------|
|    | <a href="#">382548</a> | Fixed wheel 125 DIN-PL, PA (gray)<br>(valid from 01/31/2022)            | 2.0 Each           |
|    | <a href="#">362534</a> | Cast. whl. 125 lock., DIN PL, CNS<br>(valid from 01/31/2022)            | 2.0 Each           |
|    | <a href="#">368461</a> | Fixed wheel 125 DIN-PL crs. CNS<br>(valid from 01/31/2022)              | 2.0 Each           |
|    | <a href="#">386514</a> | Swivel castor 125 lock, DIN-PL, PA, anti.<br>(valid from 01/31/2022)    | 2.0 Each           |
|  | <a href="#">389841</a> | Bearing plate<br>(valid from 08/21/2024)                                | 2.0 Each           |
|  | <a href="#">373593</a> | Swivel castor LE-POEV 160R-FI-SG<br>843898<br>(valid from 09/12/2022)   | 2.0 Each           |
|  | <a href="#">373594</a> | Fixed castor B-POEV 160R-SG 843899<br>(valid from 09/12/2022)           | 2.0 Each           |
|  | <a href="#">373398</a> | Swivel castor LEX-POEV 160XR-SG-FI-<br>84462<br>(valid from 09/12/2022) | 2.0 Each           |
|  | <a href="#">373399</a> | WHEEL, FIXED-BX-POEV 160XR-SG-<br>844626<br>(valid from 09/12/2022)     | 2.0 Each           |



| Image | Code                          | Name                                                    | Quantity in device |
|-------|-------------------------------|---------------------------------------------------------|--------------------|
|       | <a href="#"><u>387317</u></a> | 3-sided gallery undercounter<br>(valid from 01/31/2022) | 1.0 Each           |
|       | <a href="#"><u>387316</u></a> | 4-sided gallery undercounter<br>(valid from 01/31/2022) | 1.0 Each           |