

Sparepart documentation

[BPT E 2 x 18 duo H/H](#)

Prod. No.: 386611



Product details:

B.PROTHERM E 2 x 18 x 1/1 duo heated/heated
B.PROTHERM E food transport container 1/1, convection-heated
Made of corrosion-resistant steel, with hinged doors, mobile.
2 x 18 pairs of support ledges
Space between ledges: 38.3 mm
left compartment: convection-heated
right compartment: convection-heated
Temperature range adjustable between +30 °C and +95 °C.
Mains frequency: 50/60 Hz

Spareparts







Image	Code	Name	Quantity in device
	388087	Insert (valid from 02/21/2022)	2.0 Each
	388101	Comfort opening right without drawbar (valid from 02/21/2022)	1.0 Each
	144218	PLUG-LAMINATE- 40X40X1,25 SERIES 120 (valid from 09/07/2022)	2.0 Each
	83031	washer A 8.4 DIN 125 brass (valid from 09/07/2022)	3.0 Each
	388103	Comfort opening left (valid from 02/21/2022)	1.0 Each
	386646	Spring VD-165 (valid from 07/28/2022)	1.0 Each
	246508	Pressure spring D-180-03 FA. GUTEKUNST (valid from 07/28/2022)	2.0 Each
	388136	Mounting bracket 80° (valid from 02/21/2022)	2.0 Each

Image	Code	Name	Quantity in device
	<u>386649</u>	Corpus hinge top right (valid from 02/21/2022)	1.0 Each
	<u>374840</u>	Rubber buffer D25xh12-d5 (valid from 02/21/2022)	2.0 Each
	<u>386786</u>	Tube D28x1 L=586,4 (valid from 02/21/2022)	1.0 Each
	<u>372911</u>	body for push handle holder (valid from 02/21/2022)	2.0 Each
	<u>372913</u>	Cover push handle holder left, logo (valid from 02/21/2022)	1.0 Each
	<u>372912</u>	Cover push handle holder right, logo (valid from 02/21/2022)	1.0 Each
	<u>386652</u>	Hinge (valid from 02/21/2022)	2.0 Each
	<u>387303</u>	Warm module cpl. 760W (valid from 02/21/2022)	2.0 Each
	<u>107469</u>	Radial Fan R2K150/0020-4218 (valid from 02/21/2022)	1.0 Each
	<u>388233</u>	Spring 6,9x8 VD_063H_20_1 (valid from 11/02/2022)	1.0 Each








Image	Code	Name	Quantity in device
	107673	Tubular heater 760W 20.43035.000 (valid from 02/21/2022)	1.0 Each
	107694	Temperature sensor PT1000_B. PROTHERM (valid from 02/21/2022)	1.0 Each
	105805	Safety temperature limiter 135 °C (valid from 02/21/2022)	1.0 Each
	386579	mold without lock (valid from 02/21/2022)	1.0 Each
	386581	mold with lock (valid from 02/21/2022)	1.0 Each
	386673	Lock (valid from 02/21/2022)	1.0 Each
	70914	Allen screw ISO 7380 M5x8 A2 m. FI. (valid from 02/21/2022)	1.0 Each
	386903	Key (valid from 02/21/2022)	2.0 Each










Image	Code	Name	Quantity in device
	386771	Spring cpl. (valid from 11/29/2022)	1.0 Each
	388138	Knob cpl. (valid from 02/21/2022)	1.0 Each
	386565	Door handle (valid from 02/21/2022)	1.0 Each
	387941	Emergency opening (valid from 12/02/2024)	1.0 Each
	377734	Pressure spring VD-180-07 (valid from 08/03/2022)	2.0 Each
	386562	Cover (valid from 02/21/2022)	1.0 Each
	389058	Bushing (valid from 02/21/2022)	1.0 Each
	386778	Seal (valid from 02/21/2022)	2.228 Meter
	389005	Ventilation flap (valid from 08/09/2024)	1.0 Each
	365428	O-RING, 67.00 X 1.50 EPDM70 (valid from 02/21/2022)	1.0 Each
	386580	Retaining tube for ventilation flap (valid from 02/21/2022)	1.0 Each













Image	Code	Name	Quantity in device
	386547	Display Mount (valid from 02/21/2022)	2.0 Each
	107664	BPT Display (valid from 02/21/2022)	2.0 Each
	386476	Display Foil Atlas (valid from 02/21/2022)	2.0 Each
	369654	Plug holder universal (valid from 02/21/2022)	1.0 Each
	117766	plastic cover ring for plug holder (valid from 02/21/2022)	1.0 Each
	105429	terminal block Wieland KL 24/3 SL (valid from 02/21/2022)	2.0 Each
	107722	BPT Power PCB (valid from 02/21/2022)	2.0 Each
	106304	Cable gland M20x1.5 black (valid from 02/21/2022)	1.0 Each
	106311	Hexagon nut M20x1.5 (plastic) (valid from 02/21/2022)	1.0 Each
	106708	magnetic switch MK4-1A75-C-300W (valid from 02/21/2022)	2.0 Each
	107692	Decal equipotential bonding (valid from 02/21/2022)	1.0 Each
	107682	Spiral cable Europe 3x1,5 qmm BL-570 (valid from 05/23/2022)	1.0 Each
















Image	Code	Name	Quantity in device
	107683	Spiral cable UK 3x1,5 qmm BL-570 (13A) (valid from 02/21/2022)	1.0 Each
	107684	Spiral cable CH 3x1,5 qmm BL-570 (10A) (valid from 02/21/2022)	1.0 Each
	107687	Spiral cable AUS 3x1,5 qmm B-570 10A (valid from 02/21/2022)	1.0 Each
	107689	Spiral cable Denmark 3x1,5 qmm B-570 13A (valid from 02/21/2022)	1.0 Each
	107715	Protective-socket Swiss-Standard T13 bla (valid from 02/21/2022)	1.0 Each
	106803	Build-in socket British standard (valid from 02/21/2022)	1.0 Each
	106822	Safety socket Denmark (valid from 02/21/2022)	1.0 Each
	106737	Build-in socket with pin (valid from 02/21/2022)	1.0 Each
	107716	Socket outlet protective contact-black (valid from 02/21/2022)	1.0 Each
	106891	seal for ABL electrical outlets (valid from 02/21/2022)	1.0 Each

Image	Code	Name	Quantity in device
	<u>386501</u>	Swivel castor 125 lock., DIN-PL (gray) (valid from 02/21/2022)	2.0 Each
	<u>382548</u>	Fixed wheel 125 DIN-PL, PA (gray) (valid from 02/21/2022)	2.0 Each
	<u>362534</u>	Cast. whl. 125 lock., DIN PL, CNS (valid from 02/21/2022)	2.0 Each
	<u>368461</u>	Fixed wheel 125 DIN-PL crs. CNS (valid from 02/21/2022)	2.0 Each
	<u>386514</u>	Swivel castor 125 lock, DIN-PL, PA, anti. (valid from 02/21/2022)	2.0 Each
	<u>389841</u>	Bearing plate (valid from 08/21/2024)	2.0 Each
	<u>373392</u>	Castor wheel with brake LE-VPP160R-FI-SG (valid from 02/21/2022)	2.0 Each
	<u>373393</u>	FIXED WHEEL B-VPP 160R-SG (valid from 02/21/2022)	2.0 Each
	<u>373593</u>	Swivel castor LE-POEV 160R-FI-SG 843898 (valid from 02/21/2022)	2.0 Each

Image	Code	Name	Quantity in device
	<u>373594</u>	Fixed castor B-POEV 160R-SG 843899 (valid from 02/21/2022)	2.0 Each
	<u>146794</u>	CASTER WHEEL LX-VPP 160XR-FI-SG (valid from 02/21/2022)	2.0 Each
	<u>146795</u>	FIXED WHEEL BX-VPP 160XR-SG (valid from 02/21/2022)	2.0 Each
	<u>373398</u>	Swivel castor LEX-POEV 160XR-SG-FI-84462 (valid from 02/21/2022)	2.0 Each
	<u>373399</u>	WHEEL, FIXED-BX-POEV 160XR-SG-844626 (valid from 02/21/2022)	2.0 Each