

# Sparepart documentation



## BPT E 2 x 30 duo H/H

Prod. No.: 386612

### Product details:

B.PROTHERM E 2 x 30 x 1/1 duo heated/heated  
B.PROTHERM E food transport container 1/1, convection-heated  
Made of corrosion-resistant steel, with hinged doors, mobile.  
2 x 30 pairs of support ledges  
Space between ledges: 38.3 mm  
left compartment: convection-heated,  
right compartment: convection-heated,  
temperature range adjustable between +30 °C and +95 °C.  
Mains frequency: 50/60 Hz

### Spareparts

Image	Code	Name	Quantity in device
	<a href="#">388087</a>	Insert (valid from 02/16/2022)	2.0 Each
	<a href="#">388101</a>	Comfort opening right without drawbar (valid from 02/16/2022)	1.0 Each
	<a href="#">144218</a>	PLUG-LAMINATE- 40X40X1,25 SERIES 120 (valid from 09/07/2022)	2.0 Each
	<a href="#">83031</a>	washer A 8.4 DIN 125 brass (valid from 09/07/2022)	3.0 Each
	<a href="#">388103</a>	Comfort opening left (valid from 02/16/2022)	1.0 Each
	<a href="#">386646</a>	Spring VD-165 (valid from 07/28/2022)	1.0 Each
	<a href="#">246508</a>	Pressure spring D-180-03 FA. GUTEKUNST (valid from 07/28/2022)	2.0 Each
	<a href="#">388136</a>	Mounting bracket 80° (valid from 02/16/2022)	2.0 Each

Image	Code	Name	Quantity in device
	<a href="#"><u>386649</u></a>	Corpus hinge top right (valid from 02/16/2022)	1.0 Each
	<a href="#"><u>374840</u></a>	Rubber buffer D25xh12-d5 (valid from 02/16/2022)	2.0 Each
	<a href="#"><u>386786</u></a>	Tube D28x1 L=586,4 (valid from 02/16/2022)	1.0 Each
	<a href="#"><u>372911</u></a>	body for push handle holder (valid from 02/16/2022)	2.0 Each
	<a href="#"><u>372913</u></a>	Cover push handle holder left, logo (valid from 02/16/2022)	1.0 Each
	<a href="#"><u>372912</u></a>	Cover push handle holder right, logo (valid from 02/16/2022)	1.0 Each
	<a href="#"><u>386652</u></a>	Hinge (valid from 02/16/2022)	2.0 Each
	<a href="#"><u>387165</u></a>	Warm module cpl. 950 W (valid from 02/16/2022)	2.0 Each
	<a href="#"><u>107469</u></a>	Radial Fan R2K150/0020-4218 (valid from 02/16/2022)	1.0 Each
	<a href="#"><u>388233</u></a>	Spring 6,9x8 VD_063H_20_1 (valid from 11/02/2022)	1.0 Each








Image	Code	Name	Quantity in device
	<a href="#">107672</a>	Tubular heater 950W 20.43035.010 (valid from 02/16/2022)	1.0 Each
	<a href="#">107694</a>	Temperature sensor PT1000_B. PROTHERM (valid from 02/16/2022)	1.0 Each
	<a href="#">105805</a>	Safety temperature limiter 135 °C (valid from 02/16/2022)	1.0 Each
	<a href="#">386579</a>	mold without lock (valid from 02/16/2022)	1.0 Each
	<a href="#">386581</a>	mold with lock (valid from 02/16/2022)	1.0 Each
	<a href="#">386673</a>	Lock (valid from 02/16/2022)	1.0 Each
	<a href="#">70914</a>	Allen screw ISO 7380 M5x8 A2 m. FI. (valid from 02/16/2022)	1.0 Each
	<a href="#">386903</a>	Key (valid from 02/16/2022)	2.0 Each







Image	Code	Name	Quantity in device
	<a href="#">386766</a>	Push Rod 30 (valid from 02/16/2022)	1.0 Each
	<a href="#">386771</a>	Spring cpl. (valid from 11/29/2022)	1.0 Each
	<a href="#">388138</a>	Knob cpl. (valid from 02/16/2022)	1.0 Each
	<a href="#">386565</a>	Door handle (valid from 02/16/2022)	1.0 Each
	<a href="#">387941</a>	Emergency opening (valid from 12/02/2024)	1.0 Each
	<a href="#">377734</a>	Pressure spring VD-180-07 (valid from 08/03/2022)	2.0 Each
	<a href="#">386562</a>	Cover (valid from 02/16/2022)	1.0 Each
	<a href="#">389058</a>	Bushing (valid from 02/16/2022)	1.0 Each














Image	Code	Name	Quantity in device
	<a href="#">386778</a>	Seal (valid from 02/16/2022)	3.188 Meter
	<a href="#">389005</a>	Ventilation flap (valid from 08/09/2024)	1.0 Each
	<a href="#">365428</a>	O-RING, 67.00 X 1.50 EPDM70 (valid from 02/16/2022)	1.0 Each
	<a href="#">386580</a>	Retaining tube for ventilation flap (valid from 02/16/2022)	1.0 Each
	<a href="#">387946</a>	Emergency opening left (valid from 12/02/2024)	1.0 Each
	<a href="#">386547</a>	Display Mount (valid from 02/21/2022)	2.0 Each
	<a href="#">107664</a>	BPT Display (valid from 02/21/2022)	2.0 Each
	<a href="#">386476</a>	Display Foil Atlas (valid from 02/21/2022)	2.0 Each
	<a href="#">369654</a>	Plug holder universal (valid from 02/21/2022)	1.0 Each
	<a href="#">117766</a>	plastic cover ring for plug holder (valid from 02/16/2022)	1.0 Each
	<a href="#">105429</a>	terminal block Wieland KL 24/3 SL (valid from 02/21/2022)	2.0 Each
	<a href="#">107722</a>	BPT Power PCB (valid from 02/21/2022)	2.0 Each











Image	Code	Name	Quantity in device
	<a href="#"><u>106304</u></a>	Cable gland M20x1.5 black (valid from 02/21/2022)	1.0 Each
	<a href="#"><u>106311</u></a>	Hexagon nut M20x1.5 (plastic) (valid from 02/21/2022)	1.0 Each
	<a href="#"><u>106708</u></a>	magnetic switch MK4-1A75-C-300W (valid from 02/21/2022)	2.0 Each
	<a href="#"><u>107692</u></a>	Decal equipotential bonding (valid from 02/21/2022)	1.0 Each
	<a href="#"><u>107682</u></a>	Spiral cable Europe 3x1,5 qmm BL-570 (valid from 05/23/2022)	1.0 Each
	<a href="#"><u>107683</u></a>	Spiral cable UK 3x1,5 qmm BL-570 (13A) (valid from 02/21/2022)	1.0 Each
	<a href="#"><u>107684</u></a>	Spiral cable CH 3x1,5 qmm BL-570 (10A) (valid from 02/21/2022)	1.0 Each
	<a href="#"><u>107687</u></a>	Spiral cable AUS 3x1,5 qmm B-570 10A (valid from 02/21/2022)	1.0 Each
	<a href="#"><u>107689</u></a>	Spiral cable Denmark 3x1,5 qmm B-570 13A (valid from 02/21/2022)	1.0 Each
	<a href="#"><u>107715</u></a>	Protective-socket Swiss-Standard T13 bla (valid from 02/21/2022)	1.0 Each




Image	Code	Name	Quantity in device
	<a href="#">106803</a>	Build-in socket British standard (valid from 02/21/2022)	1.0 Each
	<a href="#">106822</a>	Safety socket Denmark (valid from 02/21/2022)	1.0 Each
	<a href="#">106737</a>	Build-in socket with pin (valid from 02/21/2022)	1.0 Each
	<a href="#">107716</a>	Socket outlet protective contact-black (valid from 02/21/2022)	1.0 Each
	<a href="#">106891</a>	seal for ABL electrical outlets (valid from 02/21/2022)	1.0 Each
	<a href="#">373397</a>	Swivel castor LEX-POEV 160XR-SG-844624 (valid from 02/16/2022)	2.0 Each
	<a href="#">373398</a>	Swivel castor LEX-POEV 160XR-SG-FI-84462 (valid from 02/16/2022)	2.0 Each
	<a href="#">373399</a>	WHEEL, FIXED-BX-POEV 160XR-SG-844626 (valid from 02/16/2022)	2.0 Each
	<a href="#">373393</a>	FIXED WHEEL B-VPP 160R-SG (valid from 02/16/2022)	2.0 Each
	<a href="#">373394</a>	CASTER WHEEL LE-VPP 200R-SG (valid from 02/16/2022)	2.0 Each

Image	Code	Name	Quantity in device
	<a href="#">373395</a>	CASTER WHEEL LE-VPP 200R-FI-SG (valid from 02/16/2022)	2.0 Each
	<a href="#">373396</a>	FIXED WHEEL B-VPP 200R-SG- 763618 (valid from 02/16/2022)	2.0 Each
	<a href="#">373400</a>	WHEEL, CASTER-LEX-POEV 200XR-SG-844628 (valid from 02/16/2022)	2.0 Each
	<a href="#">373401</a>	WHEEL, CASTER LEX-POEV 200XR-SG-844629 (valid from 02/16/2022)	2.0 Each
	<a href="#">373402</a>	Fixed castor BX-POEV 200XR-SG-844630 (valid from 02/16/2022)	2.0 Each
	<a href="#">373391</a>	Castor wheel LE-VPP 160R-SG (valid from 02/16/2022)	2.0 Each
	<a href="#">373392</a>	Castor wheel with brake LE-VPP160R-FI-SG (valid from 02/16/2022)	2.0 Each
	<a href="#">373593</a>	Swivel castor LE-POEV 160R-FI-SG 843898 (valid from 09/12/2022)	2.0 Each

Image	Code	Name	Quantity in device
	<a href="#">373594</a>	Fixed castor B-POEV 160R-SG 843899 <i>(valid from 09/12/2022)</i>	2.0 Each