

# Sparepart documentation




## BPT 620 KBUHE-F



Prod. No.: 392727





### Product details:


B.PROTHERM 620 KBUHE-F<br>Synthetic food -F transport container, convection-heated;<br>with tool-free removable heating element, <br>with hinged door, can be swivelled 270°; mobile.<br>12 pairs of support ledges<br>Space between ledges: 39 mm<br>Max. temperature +90 °C<br>Mains frequency: 50/60 Hz<br><br>Capacity: 3x GN 1/1-150 or its subdivisions<br>

## Spareparts

| Image                                                                               | Code                   | Name                                                              | Quantity in device |
|-------------------------------------------------------------------------------------|------------------------|-------------------------------------------------------------------|--------------------|
|    | <a href="#">121804</a> | Rep. Set BPT power cord L=2,2m<br>(valid from 02/16/2026)         | 1.0 Each           |
|   | <a href="#">121807</a> | Rep. Set BPT power cord type 360 (GB)<br>(valid from 02/16/2026)  | 1.0 Each           |
|  | <a href="#">121806</a> | Rep. Set BPT power cord CEE<br>(valid from 02/16/2026)            | 1.0 Each           |
|                                                                                     | <a href="#">121810</a> | Rep. Set BPT power cord L=2,2m (CH)<br>(valid from 02/16/2026)    | 1.0 Each           |
|  | <a href="#">121808</a> | Rep. Set BPT power cord type 325 (DK)<br>(valid from 02/16/2026)  | 1.0 Each           |
|                                                                                     | <a href="#">121809</a> | Rep. Set BPT power cord type 320 (AUS)<br>(valid from 02/16/2026) | 1.0 Each           |
|  | <a href="#">365437</a> | rep-kit BPT 620 KUF/KB/-F carcass<br>(valid from 02/16/2026)      | 1.0 Each           |
|  | <a href="#">120686</a> | rep-kit BPT 620 KUF/KB/-F carcass<br>(valid from 02/16/2026)      | 1.0 Each           |

| Image                                                                               | Code                          | Name                                                                | Quantity in device |
|-------------------------------------------------------------------------------------|-------------------------------|---------------------------------------------------------------------|--------------------|
|    | <a href="#"><u>128632</u></a> | Rep. Set handles for BPT 420/620 K blue<br>(valid from 02/16/2026)  | 1.0 Each           |
|    | <a href="#"><u>120683</u></a> | Rep-kit handles for BPT 420/620 K grey<br>(valid from 02/16/2026)   | 1.0 Each           |
|    | <a href="#"><u>121660</u></a> | Rep-kit handles for BPT 420/620 K red<br>(valid from 02/16/2026)    | 1.0 Each           |
|    | <a href="#"><u>134030</u></a> | Rep-Set BPT 420/620 Griff gelasert 2 Stk<br>(valid from 02/16/2026) | 1.0 Each           |
|    | <a href="#"><u>386502</u></a> | Swivel castor 125, DIN-PL, (gray)<br>(valid from 02/16/2026)        | 2.0 Each           |
|  | <a href="#"><u>386501</u></a> | Swivel castor 125 lock., DIN-PL (gray)<br>(valid from 02/16/2026)   | 2.0 Each           |
|  | <a href="#"><u>128630</u></a> | Rep. Set corners BPT 420/620K blue<br>(valid from 02/16/2026)       | 1.0 Each           |
|  | <a href="#"><u>368369</u></a> | Rep-kit corners BPT 420/620K grey<br>(valid from 02/16/2026)        | 1.0 Each           |
|  | <a href="#"><u>121709</u></a> | Rep-kit corners BPT 420/620K red<br>(valid from 02/16/2026)         | 1.0 Each           |
|  | <a href="#"><u>128634</u></a> | Rep. Set BPT 620/420 fastener ab 7/10 bl<br>(valid from 02/16/2026) | 1.0 Each           |
|  | <a href="#"><u>368360</u></a> | Rep-kit fastener for BPT 420/620 K grey<br>(valid from 02/16/2026)  | 1.0 Each           |

| Image                                                                               | Code                          | Name                                                                | Quantity in device |
|-------------------------------------------------------------------------------------|-------------------------------|---------------------------------------------------------------------|--------------------|
|    | <a href="#"><u>121700</u></a> | Rep-Set BPT 620/420 fastener from 7/10 r<br>(valid from 02/16/2026) | 1.0 Each           |
|    | <a href="#"><u>139369</u></a> | door without heating module BPT 620 KB<br>(valid from 02/16/2026)   | 1.0 Each           |
|    | <a href="#"><u>121241</u></a> | door without heating module BPT 620 KB<br>(valid from 02/16/2026)   | 1.0 Each           |
|                                                                                     | <a href="#"><u>134299</u></a> | (valid from 02/18/2026)                                             | 1.0 Each           |
|    | <a href="#"><u>376118</u></a> | Rep-kit BPT 420/620 hinge > 03/2013 blue<br>(valid from 02/16/2026) | 1.0 Each           |
|    | <a href="#"><u>120422</u></a> | rep-kit BPT 420/620 hinge from 03/2013<br>(valid from 02/16/2026)   | 1.0 Each           |
|  | <a href="#"><u>134156</u></a> | Rep set BPT 420/620 hinge door side grey<br>(valid from 02/16/2026) | 1.0 Each           |
|  | <a href="#"><u>121703</u></a> | Rep-Set BPT 420/620 hinge from 03/13 red<br>(valid from 02/16/2026) | 1.0 Each           |
|  | <a href="#"><u>134258</u></a> | Rep set BPT 420/620 hinge door red<br>(valid from 02/16/2026)       | 1.0 Each           |
|  | <a href="#"><u>70746</u></a>  | LOXX safety clasp top part<br>(valid from 03/04/2026)               | 2.0 Each           |
|                                                                                     | <a href="#"><u>134291</u></a> | Rep-Set BPT 420/620 KBUHE heating module<br>(valid from 02/16/2026) | 1.0 Each           |
|                                                                                     | <a href="#"><u>134292</u></a> | Rep-Set BPT 420/620 KBUHE heating module<br>(valid from 02/16/2026) | 1.0 Each           |

| Image                                                                               | Code                          | Name                                                                | Quantity in device |
|-------------------------------------------------------------------------------------|-------------------------------|---------------------------------------------------------------------|--------------------|
|                                                                                     | <a href="#"><u>134293</u></a> | Rep-Set BPT 420/620 KBUHE heating module<br>(valid from 02/16/2026) | 1.0 Each           |
|    | <a href="#"><u>70747</u></a>  | LOXX safety clasp lower part<br>(valid from 03/04/2026)             | 2.0 Each           |
|                                                                                     | <a href="#"><u>134297</u></a> | Rep-Set mounting frame<br>(valid from 02/16/2026)                   | 1.0 Each           |
|    | <a href="#"><u>119210</u></a> | rep-kit 420/620 KBUH panel + contr. V3<br>(valid from 02/16/2026)   | 1.0 Each           |
|    | <a href="#"><u>120682</u></a> | rep-kit 420/620 KBUH panel + contr. gr<br>(valid from 02/16/2026)   | 1.0 Each           |
|    | <a href="#"><u>121673</u></a> | Rep-Set 420/620 KBUH control unit red<br>(valid from 02/16/2026)    | 1.0 Each           |
|                                                                                     | <a href="#"><u>134298</u></a> | Rep-Set BPT KB(R) UHE without control<br>(valid from 02/16/2026)    | 1.0 Each           |
|  | <a href="#"><u>107012</u></a> | BPT KB(R)UH radial fan V0 to V4<br>(valid from 02/16/2026)          | 1.0 Each           |
|  | <a href="#"><u>118731</u></a> | Rep-Set BPT KB(R)UH fan Heater.-PTC<br>(valid from 02/16/2026)      | 1.0 Each           |
|  | <a href="#"><u>118732</u></a> | Rep-kit air channel BPT 420/620 KB(R)UH<br>(valid from 02/16/2026)  | 1.0 Each           |
|  | <a href="#"><u>121803</u></a> | Rep-Set BPT KB(R)UH Electrical housing<br>(valid from 02/16/2026)   | 1.0 Each           |
|  | <a href="#"><u>107014</u></a> | Repair kit BPT KBRUH NTC sensor 10K<br>(valid from 02/16/2026)      | 1.0 Each           |

| Image                                                                              | Code                          | Name                                                               | Quantity in device |
|------------------------------------------------------------------------------------|-------------------------------|--------------------------------------------------------------------|--------------------|
|   | <a href="#"><u>128647</u></a> | rotary lock electric plug compl. BPT bl<br>(valid from 02/16/2026) | 1.0 Each           |
|   | <a href="#"><u>368400</u></a> | rotary lock electric plug compl. BPT gr<br>(valid from 02/16/2026) | 1.0 Each           |
|   | <a href="#"><u>121796</u></a> | Rep-Set flap for control unit red<br>(valid from 02/16/2026)       | 1.0 Each           |
|   | <a href="#"><u>298385</u></a> | rep-kit BPT K plugs blue (8 pieces)<br>(valid from 02/16/2026)     | 1.0 Each           |
|   | <a href="#"><u>120604</u></a> | rep-kit BPT K plugs black (8 pieces)<br>(valid from 02/16/2026)    | 1.0 Each           |
|  | <a href="#"><u>121706</u></a> | rep-kit BPT K plugs red (8 pieces)<br>(valid from 02/16/2026)      | 1.0 Each           |