

Sparepart documentation



BPT E 2 x 30 duo H/H

Prod. No.: 575207

Product details:

B.PROTHERM E 2 x 30 x 1/1 duo heated/heated
B.PROTHERM E food transport container 1/1, convection-heated
Made of corrosion-resistant steel, with hinged doors, mobile.
2 x 30 pairs of support ledges
Space between ledges: 38.3 mm
left compartment: convection-heated,
right compartment: convection-heated,
temperature range adjustable between +30 °C and +95 °C.
Mains frequency: 50/60 Hz
Base model: 386612

Spareparts







Image	Code	Name	Quantity in device
	386752	Mounting bracket (valid from 02/16/2022)	2.0 Each
	386649	Corpus hinge top right (valid from 02/16/2022)	1.0 Each
	374840	Rubber buffer D25xh12-d5 (valid from 02/16/2022)	2.0 Each
	386786	Tube D28x1 L=586,4 (valid from 02/16/2022)	1.0 Each
	372911	body for push handle holder (valid from 02/16/2022)	2.0 Each
	372913	Cover push handle holder left, logo (valid from 02/16/2022)	1.0 Each
	372912	Cover push handle holder right, logo (valid from 02/16/2022)	1.0 Each

Image	Code	Name	Quantity in device
	386652	Hinge (valid from 02/16/2022)	2.0 Each
	83031	washer A 8.4 DIN 125 brass (valid from 02/16/2022)	2.0 Each
	387165	Warm module cpl. 950 W (valid from 02/16/2022)	2.0 Each
	105913	Radial fan R2A 150-AC01-21 (valid from 02/16/2022)	2.0 Each
	107672	Tubular heater 950W 20.43035.010 (valid from 02/16/2022)	1.0 Each
	107694	Temperature sensor PT1000_B. PROTHERM (valid from 02/16/2022)	2.0 Each
	105805	Safety temperature limiter 135 °C (valid from 02/16/2022)	2.0 Each





Image	Code	Name	Quantity in device
	386579	mold without lock <i>(valid from 02/16/2022)</i>	1.0 Each
	386766	Push Rod 30 <i>(valid from 02/16/2022)</i>	1.0 Each
	386771	Spring cpl. <i>(valid from 02/16/2022)</i>	1.0 Each
	386565	Door handle <i>(valid from 02/16/2022)</i>	1.0 Each
	387941	Emergency opening <i>(valid from 03/11/2026)</i>	1.0 Each
	386562	Cover <i>(valid from 02/16/2022)</i>	1.0 Each




















Image	Code	Name	Quantity in device
	<u>389058</u>	Bushing (valid from 02/16/2022)	1.0 Each
	<u>377734</u>	Pressure spring VD-180-07 (valid from 02/16/2022)	1.0 Each
	<u>386778</u>	Seal (valid from 02/16/2022)	3.188 Meter
	<u>389005</u>	Ventilation flap (valid from 08/09/2024)	1.0 Each
	<u>365428</u>	O-RING, 67.00 X 1.50 EPDM70 (valid from 02/16/2022)	1.0 Each
	<u>386580</u>	Retaining tube for ventilation flap (valid from 02/16/2022)	1.0 Each
	<u>387946</u>	Emergency opening left (valid from 02/16/2022)	1.0 Each
	<u>107664</u>	BPT Display (valid from 02/21/2022)	2.0 Each
	<u>386476</u>	Display Foil Atlas (valid from 02/21/2022)	2.0 Each
	<u>369654</u>	Plug holder universal (valid from 02/21/2022)	1.0 Each
	<u>117766</u>	plastic cover ring for plug holder (valid from 02/16/2022)	1.0 Each
	<u>105429</u>	terminal block Wieland KL 24/3 SL (valid from 02/21/2022)	2.0 Each

Image	Code	Name	Quantity in device
	<u>107722</u>	BPT Power PCB (valid from 02/21/2022)	2.0 Each
	<u>106304</u>	Cable gland M20x1.5 black (valid from 02/21/2022)	1.0 Each
	<u>106311</u>	Hexagon nut M20x1.5 (plastic) (valid from 02/21/2022)	1.0 Each
	<u>106708</u>	magnetic switch MK4-1A75-C-300W (valid from 02/21/2022)	2.0 Each
	<u>107692</u>	Decal equipotential bonding (valid from 02/21/2022)	1.0 Each
	<u>107682</u>	Spiral cable Europe 3x1,5 qmm BL-570 (valid from 02/21/2022)	1.0 Each
	<u>373391</u>	Castor wheel LE-VPP 160R-SG (valid from 02/16/2022)	2.0 Each
	<u>373392</u>	Castor wheel with brake LE-VPP160R-FI-SG (valid from 02/16/2022)	2.0 Each