

Sparepart documentation



BPT E 2 x 18 duo H/N

Prod. No.: 575209

Product details:

B.PROTHERM E 2 x 18 x 1/1 duo heated/neutral
B.PROTHERM E food transport container 1/1, convection-heated/neutral
Made of corrosion-resistant steel, with hinged doors, mobile.
2 x 18 pairs of support ledges
Space between ledges: 38.3 mm
left compartment: convection-heated, temperature range adjustable between +30 °C and +95 °C.
right compartment: neutral
Mains frequency: 50/60 Hz
Basic model: 386614

Spareparts







Image	Code	Name	Quantity in device
	386752	Mounting bracket (valid from 02/28/2022)	2.0 Each
	386649	Corpus hinge top right (valid from 02/28/2022)	1.0 Each
	374840	Rubber buffer D25xh12-d5 (valid from 02/28/2022)	2.0 Each
	386786	Tube D28x1 L=586,4 (valid from 02/28/2022)	1.0 Each
	372911	body for push handle holder (valid from 02/28/2022)	2.0 Each
	372913	Cover push handle holder left, logo (valid from 02/28/2022)	1.0 Each
	372912	Cover push handle holder right, logo (valid from 02/28/2022)	1.0 Each

Image	Code	Name	Quantity in device
	386652	Hinge (valid from 02/28/2022)	2.0 Each
	83031	washer A 8.4 DIN 125 brass (valid from 02/28/2022)	2.0 Each
	387303	Warm module cpl. 760W (valid from 02/28/2022)	1.0 Each
	105913	Radial fan R2A 150-AC01-21 (valid from 02/28/2022)	1.0 Each
	107748	Insulating plate (valid from 02/28/2022)	1.0 Each
	107673	Tubular heater 760W 20.43035.000 (valid from 02/28/2022)	1.0 Each
	107694	Temperature sensor PT1000_B. PROTHERM (valid from 02/28/2022)	1.0 Each
	105805	Safety temperature limiter 135 °C (valid from 02/28/2022)	1.0 Each


Image	Code	Name	Quantity in device
	386579	mold without lock (valid from 02/28/2022)	1.0 Each
	386771	Spring cpl. (valid from 02/28/2022)	1.0 Each
	386565	Door handle (valid from 02/28/2022)	1.0 Each
	387941	Emergency opening (valid from 03/11/2026)	1.0 Each
	386562	Cover (valid from 02/28/2022)	1.0 Each
	389058	Bushing (valid from 02/28/2022)	1.0 Each
	377734	Pressure spring VD-180-07 (valid from 02/28/2022)	1.0 Each
	386778	Seal (valid from 02/28/2022)	1.808 Meter
	387946	Emergency opening left (valid from 02/28/2022)	1.0 Each
	389005	Ventilation flap (valid from 08/09/2024)	1.0 Each
	365428	O-RING, 67.00 X 1.50 EPDM70 (valid from 02/28/2022)	1.0 Each















Image	Code	Name	Quantity in device
	386580	Retaining tube for ventilation flap (valid from 02/28/2022)	1.0 Each
	107664	BPT Display (valid from 02/28/2022)	1.0 Each
	386476	Display Foil Atlas (valid from 02/28/2022)	1.0 Each
	369654	Plug holder universal (valid from 02/28/2022)	1.0 Each
	117766	plastic cover ring for plug holder (valid from 02/28/2022)	1.0 Each
	105429	terminal block Wieland KL 24/3 SL (valid from 02/28/2022)	1.0 Each
	107722	BPT Power PCB (valid from 02/28/2022)	1.0 Each
	106304	Cable gland M20x1.5 black (valid from 02/28/2022)	1.0 Each
	106311	Hexagon nut M20x1.5 (plastic) (valid from 02/28/2022)	1.0 Each
	106708	magnetic switch MK4-1A75-C-300W (valid from 02/28/2022)	1.0 Each
	107692	Decal equipotential bonding (valid from 02/28/2022)	1.0 Each
	107682	Spiral cable Europe 3x1,5 qmm BL-570 (valid from 02/28/2022)	1.0 Each

Image	Code	Name	Quantity in device
	386501	Swivel castor 125 lock., DIN-PL (gray) <i>(valid from 08/24/2022)</i>	2.0 Each
	382548	Fixed wheel 125 DIN-PL, PA (gray) <i>(valid from 02/28/2022)</i>	2.0 Each